


**Panel
Mounted
Modular
Cougplers**

30 μ Gold

These straight and cross wired modular couplers are useful for connecting modular components. Eight different configurations all fit into the same 0.669" x 0.906" rectangular opening. Wire contacts have 30 microinch gold plating for multiple insertions. Plastic is 94V0 rated. Color: Ivory. Flange accepts #4 or #5 mounting screws (recommended 4-40 screws must be purchased separately). Category 3 rated.

Stock No.	Mfr.'s Type	Description	EACH		
			1-9	10-24	25-99
665-0002	ECF504-4C	RJ11, 6 x 4, Crossed	2.72	2.59	2.40
665-0004	ECF504-6C	RJ12, 6 x 6, Crossed	2.62	2.50	2.32
665-0006	ECF504-6CMJ	MMJ, 6 x 6, Crossed	2.81	2.68	2.49
665-0008	ECF504-8C	RJ45, 8 x 8, Crossed	3.51	3.34	3.10
665-0010	ECF504-4S	RJ11, 6 x 4, Straight	2.72	2.59	2.40
665-0012	ECF504-6S	RJ12, 6 x 6, Straight	2.92	2.78	2.58
665-0014	ECF504-6SMJ	MMJ, 6 x 6, Straight	2.81	2.68	2.49
665-0016	ECF504-8SK	RJ45, 8 x 8 K, Straight	3.51	3.34	3.10

30 μ Gold, with 10" Wire Leads

One difficulty in using modular jacks has to do with the mounting problem on a panel. L-com has a solution to the problem, by providing a flange that mounts with two screws in a 0.669" x 0.906" rectangular opening. Choice of RJ11/12 (6 x 6) or RJ45 (8 x 8 K) usable with keyed or non-keyed plugs. Recommended 4-40 mounting screws must be purchased separately.

665-0022	ECJ504-6	RJ11/12, 6 x 6, 10" Leads	2.92	2.78	2.58
665-0024	ECJ504-8	RJ45K, 8 x 8 K, 10" Leads	3.40	3.25	3.02

665-0018. ECF440. Screws PER PK./100 4.29

**Panel Mounted USB
Type A and B Couplers, 30 μ**

This coupler is great for connecting new USB style connectors into panels, etc. One side has type A connector, the other type B conforming to requirements. Recommended 4-40 mounting screws must be purchased separately. Color: Black.

Stock No.	Mfr.'s Type	Description	EACH		
			1-9	10-24	25-99
665-0032	ECF504B-UAB	USB A and B Coupler	5.54	5.29	4.91


665-0018. ECF440. Screws PER PK./100 4.29

USB Type A and B Panel Couplers, with 10" Wire Leads

Similar to the coupler above except with wire leads to connect to equipment. Choose from type A or B connectors. Wires are 20 (2 power) and 24 (2 signal) AWG stranded wires with an additional drain to shield. Recommended 4-40 mounting screws must be purchased separately. Color: Black.


Stock No.	Mfr.'s Type	Description	EACH		
			1-9	10-24	25-99
665-0042	ECJ504-UA	USB Type A, 10" Leads	5.31	5.07	4.71
665-0044	ECJ504-UB	USB Type B, 10" Leads	5.31	5.07	4.71

665-0018. ECF440. Screws PER PK./100 4.29


**Category 5 Keystone Style
RJ45 Couplers**


Two Category 5 feed-thru modular couplers are available for mating EIA568A or B Category 5 connections. Couplers come in shielded and unshielded version, the unique offset design maintains Category 5 performance and limits depth to only 1.25". Designed to mate with keystone style holes. Color: Black.

Stock No.	Mfr.'s Type	Description	EACH		
			1-9	10-24	25-99
665-0052	UJ5T568	RJ45, 8 x 8, Unshielded	7.85	7.49	6.95
665-0054	UJ5T568S	RJ45, 8 x 8, Shielded	9.82	9.37	8.70

**Category 5 Keystone Style RJ45
16 and 32 Port Panels**


These 19" rack panels utilize the UJ5T568 and UJ5T568S couplers listed above. 16 and 32 port versions are available in shielded and unshielded configurations. Category 5 rated. Color: Black.

Mini DIN Feed-Thru Adapters


Available in Mini DIN-4, 6, and 8 female/female types. Units are nickel plated brass and utilize a 1/2" "D" hole for mounting. Contacts are gold plated.

Stock No.	Mfr.'s Type	Description	EACH		
			1-9	10-24	25-99
665-0072	MD44FF	Mini DIN-4 Adapter, F-F	7.26	6.92	6.43
665-0074	MD66FF	Mini DIN-6 Adapter, F-F	7.55	7.20	6.69
665-0076	MD88FF	Mini DIN-8 Adapter, F-F	7.85	7.49	6.95

Standard IEEE-488 GPIB Cables

The CMB cable series meets all standards of the IEEE-488 interface, conforms with normal mounting procedure and is directly compatible with Hewlett Packard®, AMP® and Amphenol®.



Stock No.	Mfr.'s Type	Length	EACH			
			Meters	Feet	1-9	10-24
665-0082	CMB24-05M	0.5	1.64	53.27	50.81	47.18
665-0084	CMB24-1M	1.0	3.28	55.85	53.28	49.47
665-0086	CMB24-2M	2.0	6.56	61.04	58.22	54.06
665-0088	CMB24-3M	3.0	9.84	66.22	63.16	58.65
665-0090	CMB24-4M	4.0	13.12	71.40	68.10	63.24
665-0092	CMB24-5M	5.0	16.40	76.58	73.05	67.83
665-0094	CMB24-6M	6.0	19.68	81.76	77.99	72.42
665-0096	CMB24-8M	8.0	26.24	92.13	87.88	81.60


IEEE-488 GPIB Bulkhead Adapters

These bulkhead adapters allow clean feed-thru connections for GPIB systems. Available in either conventional Male-Female or Female-Female configurations.

Stock No.	Mfr.'s Type	Description	EACH		
			1-9	10-24	25-99
665-0102	CIB24BA	GPIB Bulkhead Adapter, M-F	30.52	29.11	27.03
665-0104	CIB24BF	GPIB Bulkhead Adapter, F-F	32.82	31.31	29.07

62.5/125 Micron Multimode Duplex Patch Cords

L-com offers the highest quality 62.5/125 fiber optic patch cords. All assemblies use the premium grade connectors with ceramic ferrules and a PC polish. Cable is OFNR riser rated PVC. Custom lengths and types available.



Stock No.</th
