ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE





USB 3.0 A/M 9PIN
INS:BLUE(PT 300C)



LOGO COLOR: RED(PANTONE 485C)
(WORDS: Arial)

	P1		P2		P1		P2
RED	5	Power	1	ORANGE	6	RX+	9
WHITE	1	D-	2	PURPLE	7	RX-	8
GREEN	2	D+	3	DRAIN	8	Gnd	7
BLACK	3	Gnd	4	YELLOW	9	TX+	6
DRAIN	4	BRAID+DRAIN	SHELL	BLUE	10	TX-	5

FEATURES:

1. USB 3.0, 2.0 and 1.1 compliant, works with Super Speed, High, Full and low speed USB devices
2. Support USB super-speed (5 Gbps)
3. Repeater cable length is 5 meters
4. Support Plug & Play
5. Supports Windows 2000/ XP/ Vistar/ Windows 7 / Mac OS 10.X and Linux
6. PCB: **V 2.0**
7. COLOR:(BLACK)
8. Packing: Each PC / Roline Color Box.
   8 pcs / Carton

CABLE: 370-1155-1

Tolerance Inch		M/M
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

Draw FANNIE 08/25/11'

Chek

Engr

Rotronic Co., Ltd.

Title
ROLINE USB 3.0 Active Repeater Cable, 5m

Item No.: 12.04.1084

App'd

Scale NONE Units m/m Third Angle Projection

Dwg No. 320-0999 REV:A Sheet 1/2

E009 V0.1

LTR	REV.	DESCRIPTION	DATE



NOTES:

1.CABLE: UL-2725 [#28(7/0.127 T.C)×1P INS:Foam-PE+D.W(7/0.127 T.C) +AL/MY+Hot-melt-Mylar]×2C+#28(7/0.127 T.C)×1P INS:Polyolefin +#24(7/0.203 T.C)×2C INS:Polyolefin + AL/MY + B.D(85%) PVC JACKET; OD:5.5±0.15mm COLOR:BLACK(NK-K01) REV 3.0.

2.CONNECTORS:

P1: OPEN.

P2: USB 3.0 A TYPE MALE 9PIN CONTACT:15u",SHELL:NI-PLATED.

3.HOOD:MOLDED TYPE ,PVC 45P,COLOR:BLACK(NK-K01)

4.ELECTRICAL TEST:

(1)100% OPEN SHORT & MIS WIRE TEST.

(2)CONTACT RESISTANCE 3 ohm Max .

(3)INSULATION RESISTANCE 10M ohm Min .

P1		P2	P1		P2
RED	Power	1	ORANGE	RX+	9
WHITE	D-	2	PURPLE	RX-	8
GREEN	D+	3	DRAIN	Gnd	7
BLACK	Gnd	4	YELLOW	TX+	6
DRAIN	BRAID+DRAIN	SHELL	BLUE	TX-	5

DWG: 370-1155-1

Tolerance Inch		M/M
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

Draw FANNIE 08/25/11'

Chek

Engr

Rotronic Co., Ltd.

Title

ROLINE USB 3.0 Active Repeater Cable, 5m

Item No.: 12.04.1084

App'd

Scale NONE Units m/m Third Angle Projection

Dwg No. 320-0999 REV:A Sheet 2/2

E009 V.01