THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION JAN ,1992.
© COPYRIGHT 1992 By – ALL RIGHTS RESERVED.

LOC	DIST
ES	00

REVISIONS 変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED ECR-12-013273	26MAR13	K.M	E.T







1. MATERIAL; HOUSING: GLASS FILLED NYLON 6T (UL 94V-0) BLACK.
   CONTACT: PHOSPHOR-BRONZE
2. FINISH: GOLD PLATING ON CONTACT AREA AND TIN PLATING ON TINE AREA OVER NICKEL PLATING.
   GOLD PLATING THICKNESS SHOWN TABLE.
3. BOSS FOR POSITIONING: APPLY FROM 40 POSNTO 100 POSN.
4. OBSOLETE



P.C.BOARD LAYOUT
(CONNECTOR MOUNT SIDE)

a	A	b	B	c	C	D	E	F	G	H	J	THK OF GOLD	POS.	P/N
〃	〃	〃	〃	49	62.23	〃	〃	64.23	67.32	74.85	72.2	0.00076	100	2-Ⓐ 4 -4
〃	〃	〃	〃	29	36.83	〃	〃	38.83	41.92	49.45	46.8	0.00076	60	2- -2
〃	〃	〃	〃	19	24.13	〃	〃	26.13	29.22	36.75	34.1	0.00076	40	2- -1
〃	〃	〃	〃	49	62.23	〃	〃	64.23	67.32	74.85	72.2	0.0003	100	-4
〃	〃	〃	〃	39	49.53	〃	〃	51.53	54.62	62.15	59.5	0.0003	80	-3
〃	〃	〃	〃	29	36.83	〃	〃	38.83	41.92	49.45	46.8	0.0003	60	-2
〃	〃	〃	〃	19	24.13	〃	〃	26.13	29.22	36.75	34.1	0.0003	40	5179533-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 粍 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差
0 PLC ±–
1 PLC ±–
2 PLC ±–
3 PLC ±–
4 PLC ±–
ANGLES ±–

MATERIAL 材料 1

FINISH 仕上 2

GENERAL TOLERANCE
10 ≧ : ±0.2
30≧ > 10: ±0.25
100 ≧ > 30: ±0.3
ANGLES:±3°

LEAD FREE

DWN ROY HAO 31AUG04
CHK STEVEN YAO 31AUG04
APVD I.ENOMOTO 31AUG04
PRODUCT SPEC 製品規格
APPLICATION SPEC 取付適用規格
WEIGHT

TE Connectivity

NAME 名称
AMP FH CONNECTOR RECEPTACLE (VERTICAL)
13mm STACKING (HIGH TEMP TYPE)
–

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A3	00779	C-5179533	–

CUSTOMER DRAWING | SCALE 尺度 NTS | SHEET 1 OF 1 | REV A