



Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings
- PDF-QuickNet HDQ ..
- Specification Sheets
- PDF-QuickNet Cas ..
- PDF-QuickNet HDQ ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'F1ASZO-9612-10F'

Your search criteria matched only one product, shown below

F1ASZO-9612-10F



Quicknet™ HDQ Series High Density Fiber Optic Cassettes:

- Mounts to standard 19" rack rails
- Low insertion loss of 0.5dB max, per optimized cassette and 0.75dB max. per standard cassette; ensures system meets IEEE 802.3ae max. channel loss specification of < 2.6dB
- Return loss: ≥ 26dB
- Adapter housing colors follow TIA/EIA - 568-C.3 suggested color identification scheme
- Connect together with high-density female MTP* cable assemblies as interconnection network
- Significantly reduce installation time and labor by eliminating field connector termination
- Factory terminated, assembled, and 100% tested
- Insertion loss data provided on every fiber cassette
- Lifetime traceability of test data to a Q.C. number
- 10Gig OM3 50/125um fiber cassettes are tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters and up to 550 meters for OM4 at 850 nm; backward compatible with all 50/125um (OM2) MPO or MTP system

requirements

Quicknet™ Cassette Rear Cable Manager:

- Mounts horizontally to standard 19" rack rails
- Fiber Management Slack Spools can be used to manage MTP Interconnect Cable

• Part Number	F1ASZO-9612-10F
• RoHS Compliancy Status	Compliant
• Note	Intended for use in fixed installations which are outside the scope of RoHS
• Part Description	QuickNet™ HDQ Series High Density Fiber Optic Cassette; 1RU-Angled 96-fiber S-type labeling; 10Gb Optimized OM4 12-fiber MTP to LC Pre-terminated— flipped polarity.
• Pricing Description	12 Fiber High Density OM4 Fiber Optic Angled Cassette Optimized
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	0
• Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.