MICRO SWITCH
FREEPORT ILLINOIS U S A
A DIVISION OF HONEYWELL
FED MFG CODE 81529

SWITCH – TOGGLE ABOVE PANEL MOUNT

CATALOG LISTING
2TP16 SERIES
CHART 1

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



	CATALOG LISTING	4 CIRCUIT WITH BUTTON IN			ELECTRICAL DATA
		LUG SIDE (1-2, 4-5)	CENTER (1-2, 4-5)	OPPOSITE LUG (2-3, 5-6)	
	2TP16-1	ON	OFF	ON	L191 15A 125, 250, 277 VAC 1/2HP 125 VAC 1HP 250, 277 VAC 5A 125 VAC "L"
	Ⓑ	OFF	NONE	ON	
	2TP16-3	ON	NONE	ON	
	2TP16-21	NONE	OFF	ON	
	2TP16-31	NONE	ON	ON	
	2TP16-4	MOM OFF	NONE	ON	L192 10A 125, 250, 277 VAC 1/4HP 125 VAC, 1/2HP 250, 277 VAC 3A 125 VAC "L"
	2TP16-5	MOM ON	OFF	ON	
	2TP16-6	MOM ON	NONE	OFF	
	2TP16-7	MOM ON	OFF	MOM ON	
	2TP16-8	MOM ON	NONE	ON	
	2TP16-51	NONE	ON	MOM ON	
	2TP16-61	MOM ON	OFF	NONE	

NOTES
1 - MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
2 - SWITCHES WILL WITHSTAND TEMPERATURE OF 160°F
3 SCREWS FURNISHED UNASSEMBLED
4 APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITION

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED TOLERANCES ARE ±

	DIM mm	TOL. mm/in	DIM in	TOL. mm/in
NO PLACES	X	1/.04		
ONE PLACE	X.X	0.4/.016	X.X	0.8/.03
TWO PLACES	X.XX	0.15/.006	X.XX	0.38/.015
THREE PLACES			X.XXX	0.13/.005
ANGLES				

DESIGN UNITS SI METRIC ☐ US CUSTOMARY ■

WEIGHT 13 LB EST

CATALOG LISTING 2TP16 SERIES CHART 1
PAGE 1 OF 1
ISSUE M 3
2TP16 SERIES
REPLACES
RELEASE NO CO-78497
CHECK
REVISIONS
A CO-94413 J J A 8 OCT 99
B CO-95303 C S L 15 NOV 99
CHECK
CHECK KAG 7 JUL 94
CHECK
CHECK
DRAWN TSM 9 JUN 94
FORMTEK