


LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			V	REVISED PER ECO—13—000071	03JAN12	KH	MZ



- 1 PARTS PACKAGED UNASSEMBLED.
- 2 CABLE CLAMPING AREA ADJUSTABLE FROM .004 TO .055 SQ IN BY REVERSING CLAMPING INSERTS.
- 3 .329 MAXIMUM CABLE OUTSIDE DIAMETER.
- 4 BULK PACKAGED KITS TO BE ORDERED IN MULTIPLES OF 800 ONLY.
- 5 OBSOLETE PART NUMBER.
- 6 STAINLESS STEEL (NON MAGNATIC).
- 7 CABLE CLAMP WITH NON-MAGNETIC STAINLESS STEEL SCREWS.
- 8 ZINC PLATED STEEL, NON-HEXAVALENT CHROMATE.
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

7 4 BULK	6	.50 ^{±.00} _{-.05}	#5-20	1-206062-9
4 BULK	8	.50 ^{±.00} _{-.05}	#5-20	1-206062-7
INDIVIDUAL	8	.38 ^{±.00} _{-.05}	#5-20	1-206062-6
4 BULK	8	.38 ^{±.00} _{-.05}	#5-20	1-206062-5
INDIVIDUAL	8	.50 ^{±.00} _{-.05}	#5-20	1-206062-4
INDIVIDUAL	8	.62 ^{±.00} _{-.05}	#5-20	1-206062-3
7 INDIVIDUAL	6	.50 ^{±.00} _{-.05}	#5-20	1-206062-2
SUPERSEDED BY 1-206062-3	8 INDIVIDUAL	.62 ^{±.00} _{-.05}	#5-20	1-206062-1
9 OBSOLETE	SMALL PACK	.38^{±.00}_{-.05}	#5-20	1-206062-0
AMP BRAZIL USE ONLY	INDIVIDUAL	12mm^{±.0}_{-.8}	3mm-20	5 206062-9
AMP BRAZIL USE ONLY	INDIVIDUAL	10mm^{±.0}_{-.8}	3mm-20	5 206062-8
SUPERSEDED BY 1-206062-7	4 BULK	.50 ^{±.00} _{-.05}	#5-20	206062-4
SUPERSEDED BY 1-206062-4	INDIVIDUAL	.50 ^{±.00} _{-.05}	#5-20	206062-3
SUPERSEDED BY 1-206062-5	4 BULK	.38 ^{±.00} _{-.05}	#5-20	206062-2
SUPERSEDED BY 1-206062-6	INDIVIDUAL	.38 ^{±.00} _{-.05}	#5-20	206062-1
PACKAGING	SCREW FINISH	SCREW LENGTH	SCREW TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
THERMOPLASTIC

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN
A GRAFF
CHK
W.G.LENKER
APVD
-
PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

4/29/91
7-22-92
-
-
-
-
-

CUSTOMER DRAWING

TE Connectivity

CABLE CLAMP KIT, STANDARD,
SHELL SIZE 11, CPC

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-206062

RESTRICTED TO
-

SCALE
NTS

SHEET
1 OF 1

REV
V