

For more Information
please call

1-800-Belden1



General Description:

Stranded silver-coated copper conductor insulation with extruded TFE Teflon.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
1	30	7x38	SPC - Silver Plated Copper

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
TFE - Tetrafluoroethylene	0.1524

Overall Insulation

Overall Cable

Overall Nominal Diameter: 0.610 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL Rating:	105°C
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Military Specification:	NEMA HP3, MIL-W-16878/6
MIL Spec Rating:	250 V, 200°C

Flame Test

UL Flame Test: VW-1

Plenum/Non-Plenum

Plenum (Y/N): No

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
83043 002100	30 MT	0.045 KG	RED	E	#30 STR TFE RED
83043 0021000	305 MT	0.454 KG	RED	E	#30 STR TFE RED

83043 Hook-up/Lead - UL AWM Style 1371

83043 005100	30 MT	0.045 KG	GREEN, DARK	E	#30 STR TFE GRNDK
83043 0051000	305 MT	0.454 KG	GREEN, DARK	E	#30 STR TFE GRNDK
83043 0071000	305 MT	0.454 KG	VIOLET	E	#30 STR TFE VIO
83043 008100	30 MT	0.045 KG	GRAY	E	#30 STR TFE GRY
83043 009100	30 MT	0.045 KG	WHITE	E	#30 STR TFE WHT
83043 0091000	305 MT	0.454 KG	WHITE	E	#30 STR TFE WHT
83043 010100	30 MT	0.045 KG	BLACK	E	#30 STR TFE BLK
83043 0101000	305 MT	0.454 KG	BLACK	E	#30 STR TFE BLK

Notes:

E = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'

Revision Number: 2 Revision Date: 07-10-2012

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.