





NOTES:

MATERIAL
1.Insulator Material:PBT+30%G.F,(UL94V-0),Grey
2.Contact Material : Brass
3.Contact Plating : 1u" Au selective Over Ni
ELECTRICAL
1.Current Rating : 3.0 AMP
2.Withstand Voltage : 1000V AC/minute
3.Contact Resistance : 20mΩ max
4.Insulation Resistance: 1000MΩ min
ENVIRONMENTAL
1.Operation Temperature: -40°C to +105°C
⑦ 2.Packing : Tube
3.10P~18P with slot"M" without slot "N"
20P-64P with slot "M" and "N"

Ordering Information

AWH xxG-E2x2-IDC

No. of Contacts : 10,14,16,20,26, 30,34,40,50,60,64

Latch Type
0 -without latch
2 -with short latches
3 -with long latches



without Latch



with short Latch



with long Latch





Short Latch



Long Latch

RoHS compliant
Unit: mm

⑥ UL File No.: E198287

Scale	Free
TOLERANCE	
X.X	±0.40
X.XX	±0.25
X.XXX	±0.15
ANGLE	±3°
DIM	TOL

Id.	Modification	Date	Name
⑨	Correct the dimension L =4.10mm	20.12.2017	Winnie
⑧	Modify the shape of insulator	05.06.2017	Winnie
⑦	Change the packing tray into tube	21.09.2015	Winnie
⑥	Add UL file no.	12.12.2013	Amy
⑤	Update	03.04.2013	Winnie
④	Correct drawing of short latch	05.05.2010	Dean

	Date	Name
Drawn	29.05.2006	Hellwig
Approved	20.19.2017	Winnie

ASSMANN WSW components

Customer-No.

ASSMANN WSW-No.
AWH xxG-E2x2-IDC

Drawing-No.
ASS 0532 CO

rev09

Replace

Sheet