THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION MAR ,1988.
© COPYRIGHT 1988 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST
J	

REVISIONS 変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REV PER ECO-10-000443	15JAN10	KK	AEG

30,50 POS 40,60 POS





E–E
SCALE 5:1



30,50 POS
(コネクタ搭載面側)
ON BOARD SIDE



20,40,60 POS
(コネクタ搭載面側)
ON BOARD SIDE

1 USE A P.C.B. WHOSE ARE TREATED WITH SOLDER RESIST.
2 SHOW P.C.B LAYOUT FROM ON BOARD SURFACE SIDE.
3 NUMBER THE CONTACT IN THE P.C.B OR CONNECTOR CONSECUTIVEELY FROM "DATUM" SIDE.
4 HOUSING MATERIAL : P.B.T(UL94V-0) / BLACK
5 CONTACT MATERIAL : PHO-BRONZE
6 FINISH : NICKEL 0.00127 MIN THK. OVERALL SELECTIVE GOLD 0.00076 MIN. OR 0.0002 MIN. THK ON CONTACT AREA AND TIN 0.001 MIN THK. ON TINE AREA.
7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

1 基板の表面はレジスト処理を施すこと。
2 基板の穴寸法は、コネクタ搭載面側から示す。
3 基板及びコネクタのn数は DATUM 位置より数える。
4 ハウジング材料：P.B.T樹脂（94V-0）,色：黒色
5 コンタクト材料：燐青銅
6 コンタクト表面仕上：1.27μ MIN厚の全面ニッケル下地めっき上に接触部分は0.76μ MIN. 又は0.2μ MIN厚の金めっき、半田付部分は1μ MIN厚のすずめっき

	6-	-5	20	9	11.43	15.60	19.20	Au PL. 0.00076 MIN.
	6-	-4	60	29	36.83	41.00	44.60	
7 OBSOLETE	6-	-3	50	24	30.48	34.65	38.26	
	6-	-2	40	19	24.13	28.30	31.90	
7 OBSOLETE	6-	-1	30	14	17.78	21.95	25.55	
7 OBSOLETE		-5	20	9	11.43	15.60	19.20	Au PL. 0.0002 MIN.
		-4	60	29	36.83	41.00	44.60	
7 OBSOLETE		-3	50	24	30.48	34.65	38.26	
		-2	40	19	24.13	28.30	31.90	
	174215-1		30	14	17.78	21.95	25.55	
	PART NUMBER		POS	n	A	B	D	REMARK

鉛フリー
LEAD FREE

GENERAL TOLERANCE 一般公差
10≧ : ±0.2
30≧ > 10 : ±0.25
100≧ > 30 : ±0.3
ANGLES : ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位： 粍 MM

TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL 材料 SEE NOTE 4 5
FINISH 仕上 SEE NOTE 6

DWN	MIURA	30MAR88
CHK	K.KASHIWA	18OCT88
APVD	R.NISHIMURA	18OCT88
PRODUCT SPEC 製品規格		
APPLICATION SPEC 取付適用規格		
WEIGHT		

Tyco Electronics
Tyco Electronics AMP K.K.
Kawasaki.Japan

NAME 名称
PLUG ASSY (VERTICAL W/O SCREW HOLE)
AMPLIMITE 050 SERIES I B-TO-B CONN.

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A3	00779	C-174215	

CUSTOMER DRAWING
SCALE 尺度 2:1 SHEET 1 OF 1 REV D1

AMP 1470-19 REV 31MAR2000
05FEB04 FJ0T1198