

External SAS Cable, 4 Lane - 4xInfiniband (SFF-8470) to 4xInfiniband (SFF-8470), 3M (10-ft.)

MODEL NUMBER: **S522-03M**



Description

Tripp Lite's S522-03M External SAS Cable features SFF-8470 to SFF-8470 connectors with heavy-duty metal backshells. This 4-channel cable is constructed with a high-performance Infiniband cable, which features individually shielded parallel pairs, double EMI/RFI shielding and 6.0 Gigabytes per second performance. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- External SAS Cable, SFF-8470 to SFF-8470 - 3 Meter
- Made with High Performance Infiniband Cable
- Support data transfer rates from 3.0 up to 6.0 gigabytes per second
- SFF-8470 thumbscrew type connectors in diecast zinc housing for durability
- RoHS compliant
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

General Info	
Product Group	COMPUTER & STORAGE CABLES
OVERVIEW	
Intended Application	Connecting Drives
Cable Type	SAS
Model Type	External
INPUT	

Highlights

- Hi-Performance 3 Meter SAS External Cable
- SFF-8470 to SFF-8470
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- SAS Controllers, SAS Chassis, SAS/SATA hard Drives

Package Includes

3 Meter SAS External SFF-8470 to SFF-8470 Cable

Cable Length (ft.)	10
Cable Length (m)	3.05
UPC ASSIGNMENT	
Unit Carton UPC#	037332151988
PHYSICAL	
Color	Black
Style	Serial Attached SCSI (SAS)
CONNECTIONS	
Connector A	SFF-8470
Connector B	SFF-8470
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.