



T&B Catalog Number: L-11-40-9-C
UPC Number: 72849493303
Description: Cable Tie 40lb 11" Natural All-Nylon 100 Per Bag

Status: Active

General

Material: Nylon 6.6
Color: Natural

Dimension Information

Length (inches): 11.5
Width (inches): 0.146
Max. Wire Bundle Diameter (inches): 3
Min. Wire Bundle Diameter (inches): 1/16

Specifications

Tensile Strength (lbs.): 40
Temperature Rating: -40°F to 185°F
Flammability Rating: UL 94 V-2

Tooling

Application Tools: ERG50, QC-100, L-200, L-400-C

Packaging

T&B Order Multiple: 100
T&B Inner Pack: 100
Package in Units: 5000
Package Type: Standard
T&B Sold in UOM: Each
T&B Weight Per UOM: 3.52 lbs. per 1000


Application Support

T&B Sales Drawings: wsd-000221
Overview: Available on Website
Material Selection Guide: Available on Website
Available Colors: Available on Website

Certifications

RoHS Compliance: Yes

Certifications



NOTES:

1. MATERIAL: NYLON 6,6
2. FLAMMABILITY: UL94V-2
3. OPERATING TEMPERATURE RANGE: -40°F [-40°C] TO 185°F [85°C]
4. MINIMUM TENSILE RATING: 40 LBS [178 N]
5. MINIMUM WIRE BUNDLE: .0625 [1,59]
6. MAXIMUM WIRE BUNDLE: SEE TABLE
7. INSTALLATION TOOL/SETTING: WT199/1-3 (MS90387-1) OR ERG299/1-3

CATALOG NUMBER	MAXIMUM WIRE BUNDLE	A
L-8-40-**-**	2.000 [50,8]	8.510 [216,15]
L-8-40FL-**-**	2.000 [50,8]	8.510 [216,15]
L-11-40-**-**	3.000 [76,2]	11.287 [286,69]
L-14-40-**-**	4.000 [101,6]	14.287 [362,9]

* = COLOR CODE - 0= BLACK (OUTDOOR) 4= YELLOW 8= GRAY 17= FLUORESCENT YELLOW
 1= BROWN 5= GREEN 9= NATURAL 18= FLUORESCENT GREEN
 2= RED 6= BLUE 11= FLUORESCENT PINK 20= FLUORESCENT BLUE
 3= ORANGE 7= PURPLE 16= FLUORESCENT ORANGE

** = PACKAGING- C= STD PKG (100) D= BULK PKG (500) M= BULK PKG (1,000)


CONSULT CUSTOMER SERVICE FOR PACKAGE QUANTITY AVAILABILITY

FLUORESCENT COLORS NOT "UR" OR "CE" RECOGNIZED OR LISTED

GENERAL NOTES			
1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.			
2. DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.			
REVISIONS			
- SEE ERN (****) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: ****	ORIGINAL PROJECT NO / (ERN NO)	SHEET NO:	DRAWING NO:
	FM401182 / (2006127)	1 OF 1	WSD-000221
DESCRIPTION: 8", 11" & 14" SERIES 40 INTERMEDIATE CABLE TIES			

Thomas & Betts
 www.tnb.com

Ty-Fast® Cable Ties



- MINIATURE
- HEAVY DUTY
- INTERMEDIATE
- EXTRA HEAVY DUTY
- STANDARD
- RELEASABLE TIES

- MOUNTING HEAD
- STRIPED TIES
- RESTRICTED BUNDLE
- IDENTIFICATION TIES
- MIL-SPEC TIES


Ty-Fast® Cable Ties are available in lengths from 4" to our exclusive 48" strap. Cable Ties will satisfy bundling requirements from 1/8" to 15" and loop tensile strengths from 18 to 175 pounds.

Cable Ties are stocked in materials and colors as listed. Contact your Ty-Fast® Distributor or Customer Service Representative for availability in special materials and colors.

Where applicable, Ty-Fast® Cable Ties are UL Recognized, Mil-Spec Approved and/or QPL Listed.

State-of-the-art robotic and raw material handling equipment assures product and material integrity throughout the manufacturing process. Overall quality is achieved through statistical analysis and quality driven operator objectives. Ty-Fast® has attained Mil-Spec I-45208 quality ratings from a number of equipment manufacturers.

Ty-Fast® products are sold through stocking T&B Distributors.



I.D. TIES (page J42)

Thomas & Betts

Catamount® Cable Fastening Systems

Catamount® Cable Ties

Catamount® Ties and Terminals fit the needs of general-purpose fastening and wire terminations. Installers quickly discover that Catamount products offer durable and value-priced cable bundling for a variety of commercial and residential construction applications. Electricians can also take advantage of other benefits in stocking Catamount products in their toolboxes, such as more terminals per bag in most popular sizes than leading comparable brands.

Catamount Ties and Terminals are offered in a wide range of sizes, styles and colors and meet listing requirements for most electrical termination and fastening projects. A choice of matching tools are also offered to provide quick and reliable installations.

Miniature — Series 18

CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-4-18-9-C	4.0	1/8	Natural	100
L-4-18-0-C	4.0	1/8	Black	100
L-6-18-9-C	6.4	1/8	Natural	100
L-6-18-0-C	6.4	1/8	Black	100
L-8-18-9-C	8.0	2	Natural	100
L-8-18-0-C	8.0	2	Black	100

Bulk packages available. Contact Customer Service.

Use QC-100, L-200, L-400-C or ERG-50 Installation Tools

Intermediate — Series 30

CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-5-30-9-C	5.6	1 1/8	Natural	100
L-5-30-0-C	5.6	1 1/8	Black	100
L-8-40-9-C	8.5	2	Natural	100
L-8-40-0-C	8.5	2	Black	100
L-11-40-9-C	11.5	3	Natural	100
L-11-40-0-C	11.5	3	Black	100
L-14-40-9-C	14.5	4	Natural	100
L-14-40-0-C	14.5	4	Black	100

Bulk packages available. Contact Customer Service.

Use QC-100, L-200, L-400-C or ERG-50 Installation Tools

Standard — Series 50

CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-5-50-9-C	5.5	1	Natural	100
L-5-50-0-C	5.5	1	Black	100
L-7-50-0-C	7.5	1 1/8	Natural	100
L-7-50-9-C	7.5	1 1/8	Black	100
L-11-50-9-C	11.1	3	Natural	100
L-11-50-0-C	11.1	3	Black	100
L-14-50-9-C	14.1	4	Natural	100
L-14-50-0-C	14.1	4	Black	100

Bulk packages available. Contact Customer Service.

Use QC-100, L-200, L-400-C or ERG-50 Installation Tools

Heavy-Duty — Series 120

CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-8-120-9-C	8.0	2	Natural	100
L-8-120-0-C	8.0	2	Black	100
L-11-120-9-C	11.1	3	Natural	100
L-11-120-0-C	11.1	3	Black	100
L-14-120-9-C	14.2	4	Natural	100
L-14-120-0-C	14.2	4	Black	100
L-18-120-9-L	18.0	4 1/2	Natural	50
L-18-120-0-L	18.0	4 1/2	Black	50
L-24-120-9-L	24.2	7	Natural	50
L-24-120-0-L	24.2	7	Black	50
L-28-120-9-L	28.0	9	Natural	50
L-28-120-0-L	28.0	9	Black	50

Use L-300C or ERG-120 Installation Tool

Extra Heavy-Duty — Series 175

CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-24-175-9-L	24.0	7.2	Natural	50
L-24-175-0-L	24.0	7.2	Black	50
L-34-175-9-L	34.0	10	Natural	50
L-36-175-9-L	36.0	10 1/2	Natural	50
L-36-175-0-L	36.0	10 1/2	Black	50
L-41-175-9-L	41.0	12	Natural	50
L-41-175-0-L	41.0	12	Black	50
L-48-175-9-L	48.0	15	Natural	50
L-48-175-0-L	48.0	15	Black	50

Use L-300C Installation Tool

Identification Ties

CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-7-50ID-9-C	7.875	1 1/8	Natural	100
L-4-18ID-9-C	4.0	1/8	Natural	100

Bulk packages available. Contact Customer Service.

Use QC-100, L-200 or L-400-C Installation Tool

Sample Catalog Order:

Length: **L 4 18 9 C**
 Color: **9 C**
 Tensile Strength: **18**
 Quantity: **9 C**

4" Length, 18-lb. Tensile Strength, Natural Color, 100-Pack Quantity

Color Table

0 - Black (UV Resistant)	9 - Natural
1 - Brown	11 - Fluorescent Pink
2 - Red	16 - Fluorescent Orange
3 - Orange	17 - Fluorescent Yellow
4 - Yellow	18 - Fluorescent Green
5 - Green	20 - Fluorescent Blue
6 - Blue	
7 - Purple	
8 - Gray	