REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
A	REVISED PER ECN # T- 5871	4/13/86	GB



NOTES:

1. MATERIAL: 1-A SOCKET WAFER; INSERT MATERIAL HIGH GRADE POLYARYLENE THERMOPLASTIC
   1-B SOCKET CONTACT; COPPER ALLOY PER QQ-B-750
   1-C SOLDERSLEEVE® TERMINATOR; REFER TO RAYCHEM DWG. CTA-0068 FOR DATA.
2. FINISH: 2-A SOCKET WAFER; FINISH TO BE AS MOLDED
   2-B SOCKET CONTACT ENGAGING AREA; GOLD PLATE PER MIL-G-45204, CLASS I
   2-C CONTACT TAIL; SOLDER COATED PER QQ-S-571 Sn63
3. WAFER: WAFER DESIGNED FOR USE WITH CONNECTORS DESIGNED TO *Raychem* SPECIFICATION D-6012
4. SOCKET ONE: SOCKET NUMBER ONE MARKED IN CONTRASTING COLOR
5. WEIGHT (MAX.): LBS. .0054 | GRAMS 2.46

© Raychem Corporation 1983

SPECIFICATION CONTROL DRAWING

ITEM	QTY	PART NO.	DWG OR SPEC. NO.	DESCRIPTION

PARTS LIST

NEXT ASSY	USED ON

THIS DRAWING AND THE INFORMATION SET FORTH HEREON ARE THE PROPERTY OF RAYCHEM CORPORATION AND ARE TO BE HELD IN TRUST AND CONFIDENCE. PUBLICATION, DUPLICATION, DISCLOSURE, OR USE FOR ANY PURPOSE NOT EXPRESSLY AUTHORIZED IN WRITING BY RAYCHEM CORPORATION IS PROHIBITED.

THIRD ANGLE PROJECTION

MATERIAL ——

FINISH ——

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND TOLERENCES ARE:

DEC .XX	±.02
DEC .XXX	±.005
ANGLES	±
MM	±

DRAWN	Pierce	DATE 4-11-83
CHECKED		DATE
APPROVED		DATE 4-26-83
APPROVED		DATE 4-26-83

PROJECT NO.

Raychem

RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

TITLE
WAFER "A1" SOCKET, SPECIAL 1" FOR USE IN MTC100 2" CONNECTOR, 125°C OPERATING TEMP. FOR 20-26 AWG ROUND WIRE TERMINATION, OVAL ENTRY, MTC100 SERIES (P.A.S.S.)

B	FSCM NO. 06090	DWG NO. MTC100-YA1-008
SCALE NONE	DO NOT SCALE THIS DWG	SHEET 1 OF 1

If this document is printed it becomes uncontrolled.
Check with the web for latest revision.