


TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24B.GL00
15	39.14	33.32	25.18	24.54	19.18	D15S24B.GL00
25	53.03	47.04	39.12	38.25	33.12	D25S24B.GL00
37	69.32	63.50	55.68	54.71	49.68	D37S24B.GL00


Protection: 4 --> flash AU
6 --> 0.76μ AU

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24B.GL00LF
15	39.14	33.32	25.18	24.54	19.18	D15S24B.GL00LF
25	53.03	47.04	39.12	38.25	33.12	D25S24B.GL00LF
37	69.32	63.50	55.68	54.71	49.68	D37S24B.GL00LF

Protection: 4 --> flash AU
6 --> 0.76μ AU

PC card drilling dimensions(after plating)
(thickness 2.40±0.20mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

rev	ecn no	dr	date
C	-	-	1996/09/09
D	LS05-001	MPE	2005/03/10
E	LS05-0056	MPE	2005/06/28
F	LS06-0097	LGO	2006/07/29
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection mm	size Scale A3 2	
TOLERANCES UNLESS OTHERWISE SPECIFIED			ANGULAR	LINEAR	0.X 0.XX 0.XXX	±0.1 ±0.1 ±0.1	ECN LS06-0097
Dr	LELEON	1992/09/16	Product family		D-SUB		
Eng	PESSON	1992/09/16	Product family		D-SUB		
Chr	LEGARE	1992/09/16	Product family		D-SUB		
Appr	LEGARE	1992/09/16	Product family		D-SUB		
FCI			FEMALE CONNECTOR STD EURO		C01-8646-0125		
straight solder type for			catalog no		CUSTOMER sheet 1 of 1		
Rev.			F		F		