


LOC		DIST		REV		DATE		APP	
G	14	P	F	ZONE	LTR	DESCRIPTION	DATE	APP	DATE
				C		REV, RDRW, & SM PKG PER 0720-0040-93	3-25-93	18	DMP



AMP WIRE RANGE		UL E13286 Listed	
16-14 AWG	SOLID OR STRANDED	16-14 AWG	SOLID OR STRANDED
LR7189 Certified		MILITARY P/N AND CLASS	
16-14 AWG	SOLID OR STRANDED	NOT APPLICABLE	

1 STAMP AMP 16-14* APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	
FOR ORDER ENTRY	1-800-526-5142	

VOLTAGE RATING: NOT APPLICABLE	WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm² [2,050-5,180] CIR MILS SOLID OR STRANDED
-----------------------------------	--

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 3 PLC DEC ± ANGLES ±	FINISH TIN PLATE 0.00254 [0.00100] MIN THK PER MIL-T-10727
--	---

DR 3-26-93 TA BRINKMAN	CHK 3-26-93 DA PATTERSON	APPD 3-26-93 DE MILLER	APPD 3-26-93 JL MECKLEY	PRODUCT SPEC	APPLICATION SPEC	WEIGHT
---------------------------	-----------------------------	---------------------------	----------------------------	--------------	------------------	--------

50	LOOSE PIECE, BAG	8-33219-5
100	LOOSE PIECE, BOX	8-33219-1
---	LOOSE PIECE	33219
QUANTITY	PACKAGE TYPE	PART NO

AMP
AMP Incorporated
Harrisburg, PA 17105-3608

TERMINAL, SPADE
TONGUE, SOLISTRAND™

SIZE	CAGE CODE	DRAWING NO
10:1	00779	33219
SCALE	10:1	SHEET 1 OF 1

CUSTOMER DRAWING