Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'F9LE10H-NM6'**

Your search criteria matched only one product, shown below

F9LE10H-NM6

- Pass all TIA/EIA-568-B.3 performance requirements
- 100% factory inspected end face geometry in compliance with Telcordia GR-326-CORE, Issue 3
- Typical insertion loss per connection: 0.25dB
- UPC polished (55dB minimum return loss)
- Include color-specific keys with positive and negative keying features to visually and mechanically distinguish connections to prevent unauthorized mating with unlike keyed or non-keyed adapters
- Part of a complete keyed LC system that includes *Opti-Core*® Patch Cords and Pigtails, *OptiCam*® Pre-Polished Cam Connectors, *Opticom*® Fiber Adapter Panels (FAPs) and *Mini-Com*® Adapter Modules
- Factory terminated and 100% tested for insertion loss and return loss
- Insertion loss and return loss data recorded for every singlemode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact Customer Service for actual lead times.
Additonal keyed colors include the following: G– Violet, H– Aqua, J– Rose, K– Slate, L– Brown, P– White, Q– Charcoal, R– Lavender, S– Peach, T– Steel Blue, V– Maroon and W– Mint.

Part Number	F9LE10H-NM6
RoHS Compliancy Status	RoHS directive is not applicable
Note	Intended for use in fixed installations which are outside the scope of RoHS.
Part Description	LC (keyed H- aqua) to pigtail, LSZH, singlemode duplex patch cord, 1.6mm jacketed cable (one duplex keyed LC connector on one end and pigtail on other end) – 9/125?m.
Product Type	Keyed LSZH Patch Cords
Length (m)	6
Fiber Compatibility	9/125um
Fiber Cable Size	1.6mm
Fiber Cable Type	Jacketed
Connector 1 Type	LC Connector- Keyed H (Aqua)
Connector 2 Type	Pigtail
Flammability Rating	LSZH (Low Smoke Zero Halogen)
Key Type and Color	Keyed H- Aqua
Pricing Description	Keyed LC (H-Aqua) pigtails, SM, Duplex, LSZH, 6M
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy