



OGA DIAGONAL: 13.90 [353.10]
VA DIAGONAL: 13.18 [334.79]
PA DIAGONAL: 12.44 [316.04]



NOTES:

1. WEIGHT OF GLASS IN GRAMS: 460±10%
2. NICOMATIC HOUSING P/N: OL05
NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	LR
2	LL
3	SHIELD
4	UL
5	UR

UNITS INCHES [MM]	
TOLERANCES UNLESS OTHERWISE SPECIFIED	
.X	± .03 [.76]
.XX	± .015 [.38]
.XXX	± .015 [.38]
ANGLES	± 1°
THIRD ANGLE PROJECTION	
DO NOT SCALE DRAWING	
SCALE 1 = 1	
3M 3M TOUCH SYSTEMS METHUEN, MA USA	
© COPYRIGHT 2005 THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY AND MAY NOT BE REPRODUCED WITHOUT 3M WRITTEN PERMISSION OR USED OR DISCLOSED FOR OTHER THAN 3M AUTHORIZED PURPOSES.	
DRAWN	K. CROWLEY 9/05

F	REVISED PER CO 033533	9/11	SB
05	REVISED PER CO 030452	5/09	SEB
04	REVISED PER CO 030072	3/09	MTD
REV	CHANGE NOTICE	DATE	DRW
MARKETING DRAWING SCT32NN 13.18"			
CAD FORMAT	AUTOCAD	SHEET	1 OF 1
SIZE	DOCUMENT NO.	REV	
C	28265-MKT	F	