Product Details for 8134 -HC-5P2

No Image Available

8134 -HC-5P2

Tyco Part Number: 6 - 1437514 - 6

Active

Discrete Sockets

RoHS Compliant (Statement of Compliance)

Product Highlights:

- Socket
- Mating Pin Dia. Range = .28 - .46 mm
- Socket Length = 2.54 mm
- Gold Contact Spring Plating
- Production Application

View all Features

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- HOLTITE CONTACTS (PDF, English)
- CONTACT PLATED (REF AUGAT 8134 -HC-5P2,P3) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- AUGAT* HOLTITE* Sockets (PDF, English)

Application Specifications:

- AUGAT HOLTITE Sockets (PDF, English)

Instruction Sheets:

- None Available

CAD Files:

- None Available

List all Documents

Additional Information:

- Product Line Information

Additional Product Images:

- Product Photo

Related Products:

- Tooling

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Socket
- Socket Length (mm [in]) = 2.54 [0.100]
- Sealant = Without
- Proprietary Name = HOLTITE
- Recommended Hole Size (mm [in]) = 1.04 [0.041]

Body Related Features:

- Mating Pin Dia. Range (mm [in]) = 0.28 – 0.46 [0.011 – 0.018]
- Spring Material = Beryllium Copper

Contact Related Features:

- Contact Spring Plating = Gold
- Contact Material = Beryllium Copper

Configuration Related Features:

- Insertion Method = Hand/Semi -Automatic

Industry Standards:

- Government/Industry Qualification = No
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- Application = Production

Packaging Related Features:

- Packaging Method = Loose Piece

Other:

- Brand = AMP

© 2006 Tyco Electronics Corporation All Rights Reserved