THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
G	86

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	S	ECR-13-000998	11FEB2013	PK	HS



"C"	"B"	"A"	FINISH	WIRE RANGE	MATERIAL	PART No
1.16	1.41	2.86	1	550-650 MCM	COPPER ASTM-B-75 ANNEALED	2-324467-3
1.16	1.16	2.61	CLEANED 1			1-324467-0
						324467

1. TIN PL .000150 MIN THK MIL-T-10727
2. PART NO: 324467; .317 LB.
   PART NO: 1-324467-0; .317 LB.
   PART NO: 2-324467-3; .348 LB.
3. .045 MAX BURR ALLOWED INSIDE THE WIRE BARREL ID IN AREA OF SIGHT HOLE.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL: SEE TABLE
FINISH: SEE TABLE

DWN DK SCHRUM 4/24/89
CHK MS FEHER 4/24/89
APVD WJ VOCKROTH 11/8/89
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT 2

TE Connectivity

NAME: SPLICE, BUTT, AMPOWER
WIRE SIZE: 600 MCM

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-324467	—

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 1 | REV S

1470-19 (3/11)