

PART NAME		NON-METALLIC ENCLOSURE (STYLE E)										PART No.		NBE-10553 AND NBE-10573																					
MATERIAL:												FINISH:												INDUSTRY STANDARDS:											
SOLID BODY & COVER _____ ABS/PC BLENDED PLASTIC UL94-5VB FLAMMABILITY RATING												BODY _____ LIGHT GRAY COVER _____ LIGHT GRAY OR CLEAR PANEL _____ ANODIZED												UL508 TYPE 1, 2, 4, 4X INDOOR, 12 & 13 NEMA TYPE 1, 2, 4, 4X, 12 & 13 IEC529-IP65											
CLEAR COVER _____ POLYCARBONATE PLASTIC UL94V-0 FLAMMABILITY RATING UV STABILIZED												COVER INCLUDES GRAY POLY-URETHANE GASKET.												AIR AND MOISTURE VENTS, GALVANIZED STEEL INTERNAL PANEL AND STAINLESS STEEL LOCKING HASP ARE NOT INCLUDED, BUT CAN BE PURCHASED SEPARATELY.											
PANEL _____ 0.078 THICK ALUMINUM LATCHES & HINGES _____ NON-METALLIC WALL MOUNTING BRACKETS _____ STAINLESS STEEL												UNIT COMES COMPLETE WITH (4) WALL MOUNTING BRKTS. & (4) M5 x 10mm LG. TRUSS HD. MACHINE SCREWS (NOT SHOWN)																							
VIEW LESS COVER												VIEW LESS COVER AND SWINGFRAME PANEL												NOTE: ALL DIMENSIONS HAVE ±0.039 [±1] TOLERANCE UNLESS OTHERWISE SPECIFIED											
PART NO.		DIMENSIONS																																	
SOLID COVER	CLEAR COVER	A	B	C	D	E	F	G	H	J	K	L	M	N	P	R	S	T	U	V	W	X	Y												
NBE-10553	NBE-10573	14.640 [372]	13.750 [349]	12.768 [324]	12.158 [309]	11.643 [296]	10.824 [275]	19.170 [487]	18.330 [466]	17.392 [442]	16.690 [424]	16.138 [410]	14.760 [375]	6.666 [169]	1.185 [30]	18.500 [470]	18.335 [466]	13.980 [355]	13.810 [337]	13.271 [470]	12.516 [318]	18.110 [460]	17.088 [434]												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bud Industries:

[NBE-10553](#) [NBE-10573](#)