


Date	SYM	REVISION RECORD	AUTH	DR.	CK.
9/19/08	A	UPDATED DIM. AND MATERIAL	T.B.	B.S.	
10/07/11	B	2.2K OHM WAS 22K	T.B.	B.S.	
10/05/12	C	UPDATED UL FILE NO.	T.B.	B.S.	



SPECIFICATION:

BODY: PBT (VO) + GF, UL FILE #E130155
 COLOR: BLACK
 CENTER CONTACT: BRASS, NICKEL PLATED
 NEG. TERMINAL: SK5, GOLD PLATED
 POS. TERMINAL: P.B., GOLD PLATED
 SPRING: Ø0.8 P.B. WIRE, GOLD PLATED
 WIRE STRAIN RELIEF: PVC
 LED: RED, Ø3mm, 2.2K Ohm, 1/4 W
 FUSE: 20AMP., 6.35mm x 30mm (1/4" X 1 1/4")
 RATED AT 18 HOURS, CONTINUOUS DUTY
 20 AMP'S MAX WITH CORRECT FUSE.
 ROHS COMPLIANT

Tolerance (Inches)	 Memory Protection Devices, Inc. 200 Broad Hollow Road, Farmingdale, New York 11735		
Decimal ±.5 (.020)			Scale Drawn By B.S. Approved By T.B.
Fractional ± .8 (.030)	Title 20 AMP CIGARETTE PLUG FOR 21 OR 22.2mm DIA. SOCKETS		
Angular ± 3°	Date 10/05/12	Drawing Number APP-001-20AMP	