


# ITB 06T-XX Plug Connector Cap with Stainless Steel Chain

ITB 06T-32 XX

MIL-DTL-5015 Compatible  
Accessory

Basic Part Number  
and Shell Size Designator  
(Table I)


Finish Options  
(Table II)



## Application Notes:

1. Metal protective cover for bayonet plug connectors with stainless steel chain.
2. Standard materials configuration consists of aluminum alloy. For platings, see TABLE II finish options.
3. A broad range of other front and rear connector accessories are available.  
See our website and/or contact the factory for complete information.

**ITB 06T-XX**  
**Plug Connector Cap**  
**with Stainless Steel Chain**



**TABLE I: PLUG CONNECTOR CAP PART NUMBERS, CONNECTOR SIZE AND DIMENSIONS**

| Part Number  | Connector Size | ØA<br>Max | ØB<br>±0.1 | C<br>min | ØF<br>+0.2<br>-0 | L<br>Max |
|--------------|----------------|-----------|------------|----------|------------------|----------|
| ITB 06T-10SL | 10SL           | 22.7      | 18.2       | 108      | 4.3              | 24.0     |
| ITB 06T-14   | 14S            | 30.0      | 24.6       | 123      | 4.3              | 24.0     |
| ITB 06T-16   | 16S            | 32.5      | 27.4       | 123      | 4.3              | 24.0     |
| ITB 06T-17   | 16             | 32.5      | 27.4       | 123      | 4.3              | 33.0     |
| ITB 06T-18   | 18             | 36.4      | 30.8       | 123      | 4.3              | 33.0     |
| ITB 06T-20   | 20             | 40.5      | 34.2       | 138      | 4.8              | 33.0     |
| ITB 06T-22   | 22             | 43.5      | 37.4       | 138      | 4.8              | 33.0     |
| ITB 06T-24   | 24             | 46.5      | 40.9       | 138      | 4.8              | 33.0     |
| ITB 06T-28   | 28             | 54.0      | 46.7       | 206      | 4.8              | 33.0     |
| ITB 06T-32   | 32             | 60.0      | 53.4       | 206      | 5.6              | 34.2     |
| ITB 06T-36   | 36             | 66.2      | 59.6       | 206      | 5.6              | 34.2     |
| ITB 06T-40   | 40             | 73.0      | 65.5       | 206      | 5.6              | 34.2     |

**TABLE II**

| FINISH OPTIONS |                                                          |
|----------------|----------------------------------------------------------|
| Sym            | Description and RoHS compliant (*)                       |
| F2             | Bright Nickel Plating (*)                                |
| F6             | Black Electrodeposited Paint (*)                         |
| F7             | Black Zn-Co Plating (*)                                  |
| F8             | Olive Drab Zn-Co Plating                                 |
| F11            | Electroless Nickel (*)                                   |
|                | Omit for standard version<br>(Cadmium Olive Drab Finish) |