



LOC	DIST	REVISIONS					
AJ	17	P	LTR	DESCRIPTION	DATE	DWN	APVD
			D1	REVISION PER ECO-09-025864	19NOV2009	KF	KW
			C1	REVISED PER ECO-09-024606	31OCT09	KK	AEQ



RECOMMENDED STRIP LENGTH

- ① CABLE USED WITHOUT SPACER
- ② CABLE USED WITH SPACER
3. SEE INSTRUCTION SHEET 408-2798
4. PARTS PACKAGED UNASSEMBLED
- ⑤ USE WITH HAND TOOL FRAME 354940-1
- ⑥ USE WITH HANDTOOL 69710-1, OR
PNEUMATIC TOOL 69365 & 69365-3
- ⑦ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

△ OBSOLETE	RG-174/U & 188/U	220217-3	220210-1	220009-5	A	1.090	227194-1	—	9-328666-4	227322-8	9-227074-1	8-5227079-3
	RG-188 DOUBLE BRAID AND RG-316 DOUBLE BRAID	—	58330-1	69477-4	A	—	227194-1	—	9-329049-0	227322-8	9-413530-3	8-5227079-2
	RG-59/U,59A/U AND 59B/U	220217-2	220189-2	220187-2	A	1.090	—	227423-1	9-50428-0	221607-6	9-413530-0	8-5227079-1
	B											
	RG-62/U,62A/U AND 62B/U	220217-1	220189-1	220187-1	A	1.090	—	—	9-50427-1	221607-5	9-227074-0	8-5227079-0
	RG-58/U,58A/U,58B/U,58C/U, AND 141/U	220217-1	220189-1	220187-1	A	1.312	—	—	9-228783-0	221607-5	9-227074-0	7-5227079-5
	BELDEN 88240 AND BERK-TEK BTDC-58	220217-2	220189-2	220187-2	B	1.090	—	227423-1	9-50428-0	9-221607-6	9-413530-0	7-5227079-2
RG-62/U,62A/U AND 62B/U	A											
△ OBSOLETE	RG-59/U,59A/U AND 59B/U	—	318452-2	—	A	1.312	—	—	9-228783-0	1-221607-6	9-227074-0	6-5227079-8
	BELDEN 9907 AND RG-141A/U	220217-1	220189-1	220187-1	A	1.090	—	—	9-50427-1	1-221607-6	9-227074-0	6-5227079-7
	BELDEN 9290	—	—	220043-1	A	1.490	—	—	9-51713-3	1-221607-6	9-413530-1	6-5227079-5
△ OBSOLETE	BELDEN 9907	220217-1	220189-1	220187-1	A	1.090	—	—	9-50427-1	1-221607-6	9-227074-0	6-5227079-4
△ OBSOLETE	RG-142/U,142A/U, AND 142B/U	220217-1	220189-1	220187-1	A	1.280	—	—	9-225382-0	1-221607-6	9-227074-0	6-5227079-1
	HI TEMP RG-59/U,TIMES PL59 AND PLF59	—	220189-5	—	A	1.312	—	—	9-228784-0	221607-5	9-413530-0	5-5227079-3
△ 2 1 2	BELDEN 88240 AND BERK-TEK BTDC-58	220217-1	318452-2	—	A	1.312	—	—	9-228783-0	221607-5	9-227074-0	4-5227079-3
	RG-179/U & 187/U	220217-3	220210-1	220009-5	A	1.090	227194-1	—	9-328666-0	227322-4	9-227074-1	2-5227079-2
	RG-179/U & 187/U	220217-3	220210-1	220009-5	A	1.090	227194-1	—	9-328666-0	9-227322-1	9-413530-3	2-5227079-0
	BELDEN 8218,AMPHENOL 21-597 & BELDEN NH SPECIAL	—	58330-1	69477-4	A	1.090	—	—	9-329461-0	2-221607-2	9-413530-2	1-5227079-9
	RG-174/U & 188/U	220217-3	220210-1	220009-5	A	1.090	227194-1	—	9-328666-0	227322-8	9-227074-1	1-5227079-6
	RG-59/U,59A/U & 59B/U	220217-2	220189-2	220187-2	A	1.090	—	227423-1	9-50428-0	9-221607-6	9-413530-0	1-5227079-1
	B											
	RG-62/U,62A/U & 62B/U	220217-1	220189-1	220187-1	A	1.090	—	—	9-50427-1	9-221607-5	9-227074-0	5227079-9
	RG-58/U,58A/U,58B/U,58C/U & 141/U	220217-2	220189-2	220187-2	A	1.090	—	227423-1	9-50428-0	221607-6	9-227074-2	5227079-7
	RG-59/U,59A/U & 59B/U				B							
RG-62/U,62A/U & 62B/U	220217-1	220189-1	220187-1	A	1.280	—	—	9-225382-0	221607-5	9-227074-0	5227079-6	
	RG-58/U,58A/U,58B/U,58C/U & 141/U	220217-1	220189-1	220187-1	A	1.090	—	—	9-50427-1	221607-5	9-227074-0	5227079-5
	CABLE SIZE	DIE SET △6	DIE SET △5	CRIMP TOOL	VIEW	A	⑤ TUBING QTY=1	④ SPACER QTY=1	③ FERRULE QTY=1	② CONTACT QTY=1	① PLUG ASSY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWG J. HAVENER	29MAR2005			Tyco Electronics Corporation	
				CWK J. HAVENER	29MAR2005			Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROV J. LIPPERT	NAME	-			
		0 PLC	± -	PRODUCT SPEC		PLUG, COMMERCIAL, BNC			
		1 PLC	± -	108-12044					
		2 PLC	± -	APPLICATION SPEC					
MATERIAL	-	ANGLES	± -	FINISH	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
					WEIGHT	-	A1	00779	C=5227079
CUSTOMER DRAWING					SCALE	4:1	SHEET	1 OF 1	REV D