


THIS DOCUMENT CONTAINS DATA PROPRIETARY
TO PROJECTS UNLIMITED, INC. ANY USE OR
REPRODUCTION, IN ANY FORM, WITHOUT PRIOR
WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC.
IS PROHIBITED.
© 2003, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE (SQUARE WAVE)	3.6	V _{p-p}
OPERATING VOLTAGE RANGE	2.5 ~ 4.5	V _{p-p}
RATED CURRENT (MAX)	90	mA
COIL RESISTANCE	15±3	OHM
MINIMUM SPL @ 10 CM	87	dBA
RESONANT FREQUENCY	2,100±500	Hz
OPERATING TEMPERATURE	-30 ~ +70	°C
STORAGE TEMPERATURE	-40 ~ +85	°C
HOUSING MATERIAL	LCP	—
TERMINAL MATERIAL	Sn PLATED PHOSPHER BRONZE	—
WEIGHT	0.43	grams

REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	9/16/05	



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.

2. SPECIFICATION SUBJECT TO CHANGE
OR WITHDRAWAL WITHOUT NOTICE.

3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

FILE NAME
SMT-0821-S-R.DWG

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS, TOLERANCES ARE ±0.5 AND
ANGLES ARE ±3°.

APPROVALS	DATE
DRAWN J.A.F.	9/05
APPROVED E.P.	9/05
B.R.	9/05
DO NOT SCALE DRAWING	

projects ®
unlimited

Dayton, Ohio

TRANSDUCER(ELECTRO-MECH)

SIZE A DRAWING NO.
SMT-0821-S-R

SCALE: N.T.S.

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[SMT-0821-S-R](#)