

Crescent
5 / 16" Reversible Ratcheting Combination Wrench, SAE



◀◀ previous print close next ▶▶

Product Details	
Catalog No.	FRR10
UPC Code	037103189189
Product Style	SAE
Jaw Opening / Capacity	5 / 16 in.
Length	5.67 in. / 144 mm
Packaging	Peg Hook / Retail Packaging
Literature	Reversible_Ratcheting.pdf
Low Res. Image	FRR10_100.jpg
High Res. Image	FRR10_300.jpg
Stock Item	Normal Stock Item

Package Details (Dimensions)

Email this Page

Product Features:

- Patented "Rapid Reverse" system for faster job completion
- Reverses direction with push of a button in the most confined areas
- Patented ratchet feature turns bolt with just 5° handle swing vs. 30°
- Closed end works in places deep sockets will not reach
- Open-end jaw surfaces are parallel to within ±.0015"
- 72 tooth ratcheting mechanism receives special heat treat process
- Tool meets ANSI torque loads for standard combination wrenches
- Mirror finish chrome vanadium steel for maximum strength, durability
- Ratcheting closed end uses 12 points of contact, less stress to fastener