Search Results

Evaluate
- FAQ's
Design a Solution
- Part Drawings
- PDF-Contour Ty C..
How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'CBR2M-M10'**

Your search criteria matched only one product, shown below

CBR2M-M10

- For indoor use
- Unique design prevents wire and cable damage
- Low profile head avoids snags and reduces overall bundle size
- Outside teeth and smooth round edges protect cable jacket – ideal for high vibration applications
- Parallel-entry limits exposure to sharp edges and protects workers' arms/hands
- Fully enclosed head for consistent strength
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation

Part Number	CBR2M-M10
RoHS Compliancy Status	Compliant
Part Description	*Contour-Ty*® Cable Tie, Parallel-entry, 7.2", Miniature cross section
Product Type	Cable Ties
Material	Nylon 6.6
Color	White
CSA Certified	Yes
UL Listed (File #E56854)	Yes
UL Recognized (File #E56854)	Yes
Length (In.)	7.2
Length (mm)	183
Width (In.)	0.098
Width (mm)	2.5
CE Compliant	Yes
Cross Section	Miniature
Head Height (In.)	0.208
Head Height (mm)	5.3
Head Width (In.)	0.209
Head Width (mm)	5.3
Locking Style	Locking
Material Flammability Rating	V-2
Max. Bundle Diameter (In.)	2.00
Max. Bundle Diameter (mm)	51
Max. Continuous Use Temperature	185°F (85°C)
Min. Bundle Diameter (In.)	0.07
Min. Bundle Diameter (mm)	1.8
Min. Loop Tensile Strength (Lbs.)	18
Min. Loop Tensile Strength (N)	80
Plenum-Rated	Yes, for use in plenum or air handling spaces per NEC Sec. 300.22 (C) and (D)
Pricing Description	Cable Tie, In-Line, 7.2"L (183mm), Miniature, Nylon, White
Thickness (In.)	0.042
Thickness (mm)	1.1
Tool	GTS, GTSL, GS2B, PTS, PPTS, STS2
Min. Order UOM	PC
Min. Order Qty.	1000
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy