



.039" [1.00mm] CONTACT CENTERS RIGHT ANGLE

FEATURES

- * Accommodates .062 \pm .008" PC board
- * PA9T or PPS insulator
- * Molded-in key available
- * High reliability/high cycle hairpin bellows contact
- * 1 amp current rating
- * 150 grams normal force minimum




READOUT





DUAL (D)


TERMINATION TYPE



MOUNTING STYLE




Metal Board Lock (R)
(with no mounting ears)




SIDE MOUNTING (S)



NO MOUNTING EARS (N)



FLUSH MOUNTING (D)



THREADED INSERT (T)

