





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.






RECOMMENDED PANEL OPENING
(MAX PANEL THICKNESS: 0.06")



JACKSCREW
SPECIFICATION

APPLICATION NOTES:
ALL PINS WIRED STRAIGHT THROUGH

LABELING:
PANTONE 2945 BLUE. "L-COM" FONT MyriaMM ITALIC.
"GENDER CHANGER" FONT ARIAL BOLD, TEXT HEIGHTS; .085"
TEXT COLOR; WHITE.



OUTLINE DRAWING

Component Specifications	
Material	
Shell	Steel
Contacts/Terminals	Copper Alloy
Hardware	Brass
Insulator	PBT Fiber Reinforced (UL 94V-0 Rated)
Finish	
Shell	Tin/Nickel Plated
Contacts/Terminals	Gold Flash Plated: 1 - 1.5µ inches
Hardware	Nickel Plated
Electrical	
Current Rating	3 AMP
Insulation Resistance	1000 MΩ Min @ 500 VDC
Dielectric Withstanding Voltage	1000 VAC (for One minute)
Environmental	
Operational Temperature Range	-55°C to +105°C

CS-131

DIMENSIONS ARE IN INCHES (mm)	
UNLESS OTHERWISE SPECIFIED, TOLERANCES TO BE:	
X ± .1 [2.5] ANGLES ± 2°	
XX ± .05 [1.3]	
XXX ± .005 [0.13]	
OVERALL CABLE LENGTH TOL:	
≤ 60 [1524] ± 0 [76.2] / - 0	
> 60 [1524] +5% / -5%	
PROJ 1	

APPROVALS	DATE
DRAWN BY D.PARIAM	11/12/2001
CHECKED BY T.CLARK	11/12/2001
APPROVED BY R.CARRICK	11/13/2001
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	

L-com COMMUNICATIONS PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY		D-SUBMINIATURE	
PRODUCT DESCRIPTION			
ADPT, GNDR CHGR DB9 SLIM M/M			
SIZE	PSCM NO.	DWG. NO.	REV.
B	43321	DGB9M-OD1	G
SCALE: 2:1		CAD FILE: DGB9M-OD1.SLDRAW	SHEET 1 OF 1