REV.	DATE	DESCRIPTION
NC	12/28/00	INITIAL RELEASE



8			
7			
6			
5	FERRULE	COPPER	NICKEL
4	CONTACT PIN	BER. COPPER	GOLD
3	BARREL	BRASS	NICKEL
2	INSULATOR	TEFLON	NATURAL
1	BODY	BRASS	GOLD
	DESCRIPTION	MATERIAL	FINISH

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS

DIMENSIONS IN [ ] ARE IN INCHES FOR CUSTOMER REFERANCE ONLY

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:

0.5–6 = ± 0 2
6–30 = ± 0.4
30–120 = ± 0.6
120–315 = ± 1
315–1000 = ± 1.6
1000–2000 = ± 2.4

DO NOT SCALE DRAWING

APPROVALS		DATE
DRAWN	G.R.S.	12/28/00
CHECKED		
ISSUED		

Connector Corporation

TITLE: 1.0/2.3 CRIMP JACK (FOR 316/U CABLE)

SIZE	FSCM NO.	DWG. NO.	REV.
A	99001	282104.DWG	NC

SCALE	NA	PART NO.	282104	SHEET	1 OF 1