







NOTES:

1.Material:
① 1.1 Housing: PBT+30%GF UL94V-0, Color White
1.2 Shell: SPCC
1.3 Contact :Brass
2. FINISH:
2.1 Contact Area: Selective 30u"Au
Solder Area:Tin Plated
Under: Ni Plated
3.MECHANICAL:
3.1 Mating Force:3.57kgf Max.
3.2 Unmating Force:1.02kgf Min
3.3 Durability:1500 cycles Min
4.ELECTRICAL:
4.1 Current Rating:1.5A
4.2 Dielectric Strength:500V AC FOR 1 MINUTE
4.3 Contact Resistance:30mΩ Max
4.4 Insulation Resistance:1000 MΩ Min
5.Operating temperature: -55°C TO +85°C
6.PACKIING: Tray

RoHS compliant

Scale	Free						Date	Name
TOLERANCE						Drawn	07.06.2013	Winnie
.X	±0.30					Approved	04.04.2014	Winnie
.XX	±0.20							
.XXX	±0.10	②	Change the Pin number	04.04.2014	Winnie			
DIM	TOL	①	Change the P/NAU-Y1008-2-R to AU-Y1008-2	25.11.2013	Winnie			
X.°	±5°	⓪	Drawn	07.06.2013	Winnie			
Angle	TOL							
UNIT	mm	Id.	Modification	Date	Name			

ASSMANN WSW components

Customer-No.

ASSMANN WSW-No.
①AU-Y1008-2

Drawing-No.
ASS 5780 CO

rev02

Replace

SHEET