THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST
GP	00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	18APR06	RG	SF



5. REFERENCE ELCON SERIES 702-31-11107.

4. FINISH:
   SOCKET BODY: SILVER PLATED .0002 MIN THK. OVER NICKEL .00004 MIN THK..
   CROWN CONTACT: GOLD PLATED .000030 MIN THK. OVER NICKEL .00004 MIN THK..
   RETAINING HOOD: PASSIVATED.

3. MATERIALS:
   SOCKET BODY: COPPER ALLOY
   CROWN CONTACT: BERYLLIUM COPPER.
   RETAINING HOOD: STAINLESS STEEL.

2. ITEMS PROVIDED TO THIS SPECIFICATION SHALL BE PERMANENTLY IDENTIFIED/PACKAGED PER THE FOLLOWING: CONNECTOR PART NUMBER AND DATE CODE OF MFR.

1. PART NUMBER CHANGES AND/OR DESIGN CHANGES AFFECTING ITEM INTERCHANGEABILITY REQUIRE PRIOR ELCON APPROVAL AND AUTHORIZATION BY REVISION TO THIS DRAWING.

AS SHOWN	6648317-1
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± .02
2 PLC	± .010
3 PLC	± -
4 PLC	± -
ANGLES	± .5

MATERIAL: -

FINISH: -

DWN	R.GRZYBOWSKI	18APR2006
CHK	S.FLICKINGER	18APR06
APVD	S.FLICKINGER	18APR06
PRODUCT SPEC	—	
APPLICATION SPEC	—	
WEIGHT	—	

tyco Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME: SOCKET CONTACT, SIZE #8 CRIMP REMOVABLE STYLE
—

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-6648317	—

CUSTOMER DRAWING

SCALE	SHEET	REV
1:1	1 OF 1	A

ELCON | CIRCULAR CONTACT

AMP 1470-19 REV 31MAR2000