

REV. K

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED		TOLERANCES ARE:		TITLE:	DWG NO:
ONE PLACE DECIMALS: $\pm .1$	[2.5]	THREE PLACE DECIMALS: $\pm .005$	[.127]	ANGLES	$\pm 2^\circ$	.100 [2.54] C.L. SHUNT ASSEMBLY	SNT-100-XX-X-X
TWO PLACE DECIMALS: $\pm .01$	[.25]	FOUR PLACE DECIMALS: $\pm .0020$	[.0508]				SHEET 1 OF 1

BODY: USE SNT-100-XX
CONTACT: USE C-37-X

SNT-100-XX-X-X

OPTION

-H: HANDLE (SEE -H OPTION)

PLATING SPECIFICATION

-T = TIN: SPECIFY -T IN CONTACT SUFFIX -X

-G = GOLD: SPECIFY -G IN CONTACT SUFFIX -X

-H = HEAVY GOLD: SPECIFY -H IN CONTACT SUFFIX -X

COLOR SPECIFICATION

SPECIFY COLOR IN BODY SUFFIX -XX

BK = BLACK

RD = RED


BL = BLUE

YW = YELLOW

OR = ORANGE

CRITICAL DIMENSION INSPECTION TABLE

ASSEMBLY OPERATION	IN-PROCESS INSPECTION
FILL	C1, C2



NOTES:


1. REPRESENTS A CRITICAL DIMENSION.
2. ALTERNATE VENDOR CAVITY ID RUNNER/CAVITY (EX: AC IS RUNNER 1 CAVITY 3).

Do not scale
from this print

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SANTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED IN
ANY FORM OR BY ANY MEANS,
ELECTRONIC OR MECHANICAL,
INCLUDING PHOTOCOPYING, RECORDING,
OR BY ANY INFORMATION STORAGE
AND RETRIEVAL SYSTEM, WITHOUT THE
WRITTEN CONSENT OF SANTEC INC.

-H OPTION



BODY: USE SNH-100-XX
CONTACT: USE C-37-X

SCALE: .3

santec

MISC/MKTG
SNT-MKT

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: KOLB 1-31-90

SNT-100-XX-X-X
SHEET 1 OF 1