

Acclaim - Stock Range

Technical Specification


Accuracy class: 1.5

Deflection Angle: 90°

Movement: taut band moving coil

Operating temperature: 0-50°C

Dimensions



To surface mount, drill 2 x 8mm holes for terminals (and fixing) with centres at dimension E, F and 4 x 3.5mm holes with centres at dimensions C, D (optional).

	Window		Cover								Cut outs	
	A	B	A	B	C	D	E	F	G	H	Win	Bez
AM25	78	60	81.5	63.5	48	48	50	36	71.5	81.2	81.5	79.5
									x	x	x	x
AM35	95.5	75	99.5	78.5	57	57	50	41	27.5	36.2	36.5	33.45
									89.5	99.2	99.5	97.4
AM45	132	102	135.5	105.5	100	90	50	56	x	x	x	x
									39.5	49.2	49.5	46.4
									126	135.2	135.5	133.4
									x	x	x	x
									59	68.2	68.5	65.2