

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130102-0169](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Super-Safeway™ Rubber Hand Lamp with 100W Open End Reflector Guard W 15.24m (50.0') 16/3 SOOW

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130102](#)
NEMA Configuration NEMA 5-15
Outlet None
Overview [Hand Lamps](#)
Product Literature Order No 987650-8053
Product Name Super-Safeway™
Type Hand Lamps
UPC 78678879530
Woodhead Yes

Physical

Cord Length - Primary 15.24m (50.0')
Cord Length - Secondary N/A
Depth 153.92mm (6.060")
Duty Industrial
Guard Included No
Guard Type Metal Wire
Height 311.66mm (12.270")
Length N/A
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Hand Held
Net Weight 320.230/kg
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Cord Type - Primary 16/3 SOOW
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch No
Voltage (Fixture) - Maximum 240V

Material Info

Old Part Number 114B163



image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130102Series](#)