

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

HSTT 12 - 48 0 2


COLOR
BLANK = BLACK 5 = GREEN
1 = BROWN 6 = BLUE
2 = RED 10 = WHITE
3 = ORANGE 45 = YELLOW/GREEN
4 = YELLOW C = CLEAR

QUANTITY PER CARTON (48 IN ONLY)
0 = 25pcs.
5 = 5pcs.
2 = 2pcs.

LENGTH IN"
INCHES
.5
1
48
FEET:
M=1000
D=500
T=200
C=100
L=50
Q=25

TUBING SIZE - EXPANDED I.D.

TT = THIN WALL
TTV = THIN WALL VW-1 RATED



NOTES:

- SHRINK RATIO: 2:1
- MATERIAL: CROSSLINKED POLYOLEFIN
- "ALL WARRANTIES, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. (USER IS RESPONSIBLE TO DETERMINE SUITABILITY OF PRODUCT FOR INTENDED USE.)"
- REELS OF PRODUCT ARE ALLOWED TO HAVE SPLICES.

PACK CODE	M	D	T	C	L	Q
ALLOWED SPLICES	4	3	2	1	1	0

3	5/15/13	LEF	VJS	△	ADDED NOTE #4 ALLOWED SPLICES PER REEL LENGTH	GB0239KH	3	RAMI		
2	2/21/12	LEF		△	ADDED "CUSTOMER DRAWING" TO TITLE BLK REMOVED ALL TOLERANCES IN TITLE BLK	GB0239KH	2	RAMI		
1	10/5/11	LEF		△	ADD COLORS 1 & 3 CHANGE METRIC (19.0 TO 19.1)	GB0239KH	1	RAMI		
REV	DATE	BY	CHK		DESCRIPTION	ECN	R	CUST	SUP	

PANDUIT PART NUMBER	Min. Exp. I.D In. (mm)	Max. Rec. I.D In. (mm)	RECOVERED WALL In. (mm)
HSTT05	.046 (1.2)	.023 (.6)	.016±.003 (.406±.076)
HSTT06	.063 (1.6)	.031 (.8)	.017±.003 (.432±.076)
HSTT09	.093 (2.4)	.046 (1.2)	.020±.003 (.508±.076)
HSTT12	.125 (3.2)	.062 (1.6)	.020±.003 (.508±.076)
HSTT19	.187 (4.8)	.093 (2.4)	.020±.003 (.508±.076)
HSTT25	.250 (6.4)	.125 (3.2)	.025±.003 (.635±.076)
HSTT38	.375 (9.5)	.187 (4.8)	.025±.003 (.635±.076)
HSTT50	.500 (12.7)	.250 (6.4)	.025±.003 (.635±.076)
HSTT75	.750 (19.1)	.375 (9.5)	.030±.003 (.762±.076)
HSTT100	1.000 (25.4)	.500 (12.7)	.035±.005 (.889±.127)
HSTT150	1.500 (38.1)	.750 (19.1)	.040±.006 (1.016±.152)
HSTT200	2.000 (50.8)	1.000 (25.4)	.045±.007 (1.143±.178)
HSTT300	3.000 (76.2)	1.500 (38.1)	.050±.008 (1.270±.203)
HSTT400	4.000 (101.6)	2.000 (50.8)	.055±.009 (1.397±.229)

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS G03597HN_DC_G00239KH_PB_HSTT_03

PANDUIT

CORP. TINLEY PARK, ILLINOIS

HSTT THIN WALL HEAT SHRINKABLE TUBING CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) _____ (.XXX) _____
(.XX) _____ ANGLES ---

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY LGRAVITT

MAT'L:

SCALE NONE

DATE 5/12/03

SEE NOTES

DRAWING NO.

GB0239KH

DWG
SIZE
A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[HSTT05-Q](#) [HSTT09-48-Q10](#) [HSTT19-48-Q45](#) [HSTT05-48-Q2](#) [HSTT12-48-Q2](#) [HSTT25-48-Q2](#) [HSTT38-48-Q2](#)
[HSTT75-C2](#) [HSTT100-48-5-2](#) [HSTT38-48-Q4](#) [HSTT38-C5](#) [HSTT75-C5](#) [HSTT05-48-Q6](#) [HSTT25-48-Q6](#) [HSTT100-48-5-6](#) [HSTT38-C10](#) [HSTT50-48-5C](#) [HSTT12-48-Q45](#) [HSTT75-QC](#) [HSTT19-C2](#) [HSTT12-Q45](#) [HSTT100-C45](#)
[HSTT50-48-545](#) [HSTT150-48-5C](#) [HSTT38-C4](#) [HSTT05-MC](#) [HSTT38-QC](#) [HSTT50-48-5-10](#) [HSTT38-48-QC](#) [HSTT25-48-Q10](#) [HSTT19-CC](#) [HSTTV19-Q](#) [HSTT19-M](#) [HSTT25-48-Q5](#) [HSTT38-48-Q5](#) [HSTT200-48-5](#) [HSTT38-48-Q10](#) [HSTT50-C2](#) [HSTT12-48-Q10](#) [HSTT38-Q45](#) [HSTTV12-M](#) [HSTTV19-48-Q](#) [HSTT50-Q45](#) [HSTT75-48-545](#)
[HSTT75-48-5-4](#) [HSTT25-D2](#) [HSTT75-48-5-10](#) [HSTT50-48-QC](#) [HSTTV75-T4](#) [HSTTV75-48-CQ](#) [HSTT06-M4](#) [HSTT38-TC](#) [HSTTV09-Y](#) [HSTT50-T2](#) [HSTT05-M4](#) [HSTT50-48-Q1](#) [HSTTV06-Y](#) [HSTT06-C6](#) [HSTT100-48-5-3](#) [HSTT38-48-Q6](#) [HSTTV100-48-5](#) [HSTT38-T2](#) [HSTT12-48-TLC](#) [HSTT300-L](#) [HSTTV25-D4](#) [HSTT09-M4](#) [HSTT38-48-Q45](#) [HSTTV25-Q](#) [HSTT19-48-Q5](#) [HSTTV25-48-TL](#) [HSTT05-48-Q5](#) [HSTT12-48-Q5](#) [HSTT50-C4](#) [HSTT25-48-TLC](#) [HSTT19-48-Q6](#) [HSTT06-M10](#) [HSTT50-CC](#) [HSTT09-48-QC](#) [HSTTV09-M4](#) [HSTT09-M10](#) [HSTT75-48-CQ](#) [HSTT100-48-5-1](#) [HSTT06-QC](#) [HSTTV25-D2](#) [HSTT09-CC](#) [HSTT50-T5](#) [HSTTV06-C](#) [HSTT25-C4](#) [HSTT200-48-5-2](#) [HSTTV12-48-TL](#) [HSTTV38-T6](#) [HSTT25-QC](#) [HSTT06-48-Q5](#) [HSTT38-T4](#) [HSTT06-48-Q10](#) [HSTTV50-48-Q](#) [HSTT12-M2](#) [HSTT150-48-5-6](#) [HSTT50-C10](#) [HSTT75-C10](#)