


Connecting cables  
M12 to M12, LED  
A-coded  
male, straight -  
female, angled



| Ordering data                   |       |
|---------------------------------|-------|
| Male, straight - Female, angled |       |
| PVC                             | 1.5 m |
| PUR                             | 1.5 m |
| PUR halogen-free                | 1.5 m |
| PUR halogen-free yellow         | 1.5 m |
| Resistant to welding beads      | 1.5 m |
| Note                            |       |

| 2 LEDs                    | 3-pole     |
|---------------------------|------------|
| Type                      | Order No.  |
| SAIL-M12GM12W-3L1.5V      | 1925410150 |
| SAIL-M12GM12W-3L1.5U      | 9457790150 |
| SAIL-M12GM12W-3L1.5Q      | 1926600150 |
| SAIL-M12GM12W-3L1.5T      | 1004320150 |
| Other versions on request |            |

| 2 LEDs                    | 4-pole     |
|---------------------------|------------|
| Type                      | Order No.  |
| SAIL-M12GM12W-4-2L1.5V    | 1925420150 |
| SAIL-M12GM12W-4-2L1.5U    | 1906410150 |
| SAIL-M12GM12W-4-2L1.5Q    | 1926610150 |
| SAIL-M12GM12W-4-2L1.5T    | 1004310150 |
| Other versions on request |            |

| 3 LEDs                    | 4-pole     |
|---------------------------|------------|
| Type                      | Order No.  |
| SAIL-M12GM12W-4-3L1.5V    | 1963930150 |
| SAIL-M12GM12W-4-3L1.5U    | 1963910150 |
| SAIL-M12GM12W-4-3L1.5Q    | 1232810150 |
| SAIL-M12GM12W-4-3LW1.5QGE | 1093060150 |
| SAIL-M12GM12W-4-3LW1.5T   | 1020930150 |
| Other versions on request |            |

Standard cable lengths

|                                                                                                                                                                  |        |            |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|------------|
| All cables listed under the ordering data have a length of 1.5 metres. The last four ordering digits must be changed when ordering other standard cable lengths. | 1.5 m  | xxxxxx0150 |
|                                                                                                                                                                  | 3.0 m  | xxxxxx0300 |
|                                                                                                                                                                  | 5.0 m  | xxxxxx0500 |
|                                                                                                                                                                  | 10.0 m | xxxxxx1000 |

Technical data

|                                         |                                        |
|-----------------------------------------|----------------------------------------|
| Rated current                           | 4 A                                    |
| Protection class                        | IP 67                                  |
| Core cross-section                      | 0.34 mm²                               |
| Contact surface                         | gold-plated                            |
| Temperature range of housing            | -25...+85 °C                           |
| Rated voltage                           | 250 V (3- and 4-pole) / 125 V (5-pole) |
| (acc. to VDE standard 0110 ISO group C) |                                        |

Chapter W includes additional technical specifications for the cable

Dimensioned drawing

