



(1,27mm) .050"

DWM, HDWM SERIES

HDWM-20-58-G-S-427

HDWM-24-59-L-S-300-SM

DWM-08-56-L-D-312-SM

DWM-06-54-G-D-360

# MICRO BOARD STACKER

## SPECIFICATIONS

### DWM

For complete specifications see [www.samtec.com?DWM](http://www.samtec.com?DWM)

#### Insulator Material:

Top: Black LCP  
Bottom: Natural LCP

#### Terminal Material:

Phosphor Bronze

#### Plating:

Au or Sn over

50µ" (1,27µm) Ni

#### Current Rating:

1A

#### Operating Temp Range:

-55°C to + 105°C with Tin

-55°C to + 125°C with Gold

#### RoHS Compliant:

Yes

### HDWM

For complete specifications see [www.samtec.com?HDWM](http://www.samtec.com?HDWM)

Same as DWM except not CSA rated.

#### Processing:


Lead-Free Solderable:

Yes


SMT Lead Coplanarity:

(0,15mm) .006" max

Mates with:  
SMS, SLM, RSM



Variable  
stacker  
height



Ideal for high density  
"skyscraper"  
board stacking

| TYPE STRIP | NO. PINS PER ROW                                                       | LEAD STYLE                    | PLATING OPTION                                                                                                                       | ROW OPTION                                            | STACKER HEIGHT                                                            | OTHER OPTION                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
|------------|------------------------------------------------------------------------|-------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------|---------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|            | 01 thru 50                                                             | Specify LEAD STYLE from chart | <p>—L<br/>= 10µ" (0,25µm)<br/>Gold contact, Matte Tin on tail</p> <p>—G<br/>= 10µ" (0,25µm)<br/>Gold on post, Gold flash on tail</p> | <p>—S<br/>= Single Row</p> <p>—D<br/>= Double Row</p> | <p>—"XXX"<br/>= Stacker Height<br/>Example:<br/>-250 = (6,35mm) .250"</p> | <p>—"XXX"<br/>= Polarized Position<br/>(Specify position of omitted pin)</p> <p>—SM<br/>= Surface Mount<br/>(Requires HDWM. 02 thru 40 positions only.)</p> <p>—A<br/>= Alignment Pin<br/>(Requires HDWM. 6 positions min —D only.)<br/>Metal or plastic at Samtec discretion (N/A with —LC)</p> <p>—LC<br/>= Locking Clip<br/>(Requires HDWM. 5 positions min. —D only)<br/>(N/A with —A) (Manual placement required)</p> <p>—P<br/>= Pick &amp; Place Pad<br/>(Requires HDWM)</p> |
|            | DWM<br>= Standard Board Spacer<br><br>HDWM<br>= High Temp Board Spacer |                               |                                                                                                                                      |                                                       |                                                                           |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |

(1,27) .050 X  
No. of Positions  
(2,48) .098  
(1,27) .050 TYP  
(2,54) .100  
(4,98) .196  
(0,46) .018 SQ  
(0,51) .020  
(0,00) .000 MIN  
(2,54) .100  
(3,05) .120  
(0,51) .020 DIA

STACKER HEIGHT (5,08) .200 MIN  
(1,27) .050 TYP  
(1,27) .050  
STACKER HEIGHT (6,35) .250 MIN  
OAL

| LEAD STYLE | OAL<br>THROUGH-HOLE | SURFACE MOUNT |
|------------|---------------------|---------------|
| -01        | (11,43) .450        | (8,38) .330   |
| -51        | (10,41) .410        | —             |
| -52        | (10,80) .425        | —             |
| -53        | (12,83) .505        | (9,78) .385   |
| -54        | (14,10) .555        | (11,05) .435  |
| -55        | (15,49) .610        | (12,45) .490  |
| -56        | (15,88) .625        | (12,83) .505  |
| -57        | (16,51) .650        | (13,46) .530  |
| -58        | (17,91) .705        | (14,86) .585  |
| -59        | (19,18) .755        | (15,62) .615  |
| -60        | (20,96) .825        | —             |
| -61        | (26,67) 1.050       | —             |

**Note:** Other Gold plating options available. Contact Samtec.

**Note:** These Series are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

[WWW.SAMTEC.COM](http://WWW.SAMTEC.COM)

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC SILICON VALLEY • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-9329  
 SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0  
 SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292  
 SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766  
 SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683