




data sheet

system:	Lithium-Ion-Battery
nominal voltage:	3,7V
end charge voltage:	4,2V
max. charge current:	1400mA
charge conditions	
standard charge:	700mA for 3,5h min.
fast charge:	1400mA for 2,5h min.
charging method:	CC-CV (constant current and constant voltage)
capacity	
nominal:	after standard charge 1400mAh at 0,2C discharge to 2,75V
minimal:	1300mAh at 0,2C discharge 1250mAh at 1C discharge
max. discharge current:	2800mA
life time expectancy:	> 300 cycles
ambient temperature range	
charge:	0...45°C
discharge:	-20...60°C
storage:	-20...60°C less than 1 month -20...40°C less than 3 months -20...20°C less than 1 year
weight:	80g
dimensions:	L1: 32,1mm L2: 33,8mm h1: 45,7mm



39

	specifications for model/type:	A-Son NP FP71
	Ansmann drawing number / part number:	5060263
	drawn by / date:	Gramlich / 02.01.2006