

MTA (Mass Termination Assemblies) Printed Circuit Board Connectors




MTA-100 Post Headers — 0.100" Centers


Discrete wire to board — 2-piece interconnection. Insulation displacement wire termination. **MTA Post Headers:** 0.100" Centers. **Insulation:** Polyester. UL94V-0 rated. Natural color. **Posts:** Tin-plated copper alloy. Meets the material requirements to Table 23.1 of UL 1410 Standards for Television Receiver and Video Products*. UL Recognized File No. E 28476. CSA Certified File No. LR17189. *Wire-to-post connectors only.

0.200" Wide Flat Headers

Straight Post — 0.025" Square




Right Angle Post — 0.025" Square



512-3860	640453-2	2	0.200	.13	.12
512-3861	640453-3	3	0.300	.20	.18
512-3862	640453-4	4	0.400	.26	.24
512-3863	640453-5	5	0.500	.33	.29
512-3864	640453-6	6	0.600	.23	.20
512-3865	640453-7	7	0.700	.42	.37
512-3866	640453-8	8	0.800	.47	.43
512-3868	1-640453-0	10	1.000	.59	.53

0.092" Wide — Narrow Flat Header


Straight Post — 0.025" Square



Straight Post — 0.025" Square with Retentive Legs

Stock No.	Mfr.'s Type	No. of Pos.	Dimension A — In.	EACH	
				1-499	500-999
512-3885	644695-4	4	0.388	.28	.25

Right Angle — 0.025" Square




Right Angle — 0.025" Square with Retentive Legs

512-3923	644694-4	4	0.388	.20	.18
----------	----------	---	-------	-----	-----


Polarized Header with Polarized Notches

Straight Post — 0.025" Square




512-3300	640454-2	2	0.200	.08	.07
512-3301	640454-3	3	0.300	.08	.07
512-3302	640454-4	4	0.400	.10	.09
512-3303	640454-5	5	0.500	.11	.10
512-3304	640454-6	6	0.600	.12	.11
512-3305	640454-7	7	0.700	.14	.13
512-3306	640454-8	8	0.800	.15	.13
512-3325	640454-9	9	0.900	.57	.51
512-3307	1-640454-0	10	1.000	.18	.17
512-3329	1-640454-1	11	1.100	.69	.62
512-3308	1-640454-2	12	1.200	.28	.25
512-3332	1-640454-3	13	1.300	.82	.73
512-3309	1-640454-4	14	1.400	.88	.79
512-3310	2-640454-0	20	2.000	1.57	1.41

Right Angle Post — 0.025" Square




Friction Lock Header with Polarized Notches

Straight Post — 0.025" Square



Right Angle Post — 0.025" Square



512-3333	640457-2	2	0.200	.07	.06
512-3334	640457-3	3	0.300	.08	.07
512-3335	640457-4	4	0.400	.10	.09
512-3336	640457-5	5	0.500	.12	.10
512-3337	640457-6	6	0.600	.12	.11
512-3338	640457-7	7	0.700	.14	.13
512-3339	640457-8	8	0.800	.15	.13
512-3340	640457-9	9	0.900	.57	.51
512-3341	1-640457-0	10	1.000	.17	.15
512-8642	1-640457-2	12	1.200	.28	.25
512-8765	1-640457-4	14	1.400	.88	.79

Check Pricing And Availability Of All Items On The Internet At www.alliedelec.com

ALLIED ► 397