


# Triplexer with Integrated SAW Filter



All the technical data and information contained  
herein are subject to change without prior notice. (in mm)

Part Number	Frequency Range(P1)(f1) (MHz)	Frequency Range(P2)(f2) (MHz)	Frequency Range(P3)(f3) (MHz)	Insertion Loss (ANT-P1)(in f1) I (dB)	Insertion Loss (ANT-P2Open)(in f2) III (dB)	Insertion Loss (ANT-P2)(in f2) I (dB)	Insertion Loss (ANT-P3)(in f3) I (dB)
<b>LMTP33AA-148</b>	1575.50 ±1.5 MHz	859.0 ±35 MHz	1920.0 ±70.0 MHz	2.2 max. (at 25°C)	0.9 max. (at 25°C)	1.5 max. (at 25°C)	0.95 max. (at 25°C)