


**Note:**

To Remove mounting ring from bellows as supplied by inserting a 3.0Ø bar in one of the holes and twisting anti-clockwise through 41°. Mounting ring can be used as a template for drilling/tapping holes in mounting face.

Benefits

- ❖ Low profile easy to operate foot bellows
- ❖ For free standing applications or secured with a built in mounting plate

- ❖ Available as twin foot bellows (see 6447) and with convex top and base
- ❖ Base material - black rigid PVC, except double volume
- ❖ Bellows material - flexible PVC

6448 - - 0 0 0 0

1. Model Number**2. Tube Entry**

- A Side Entry Tube, Flat Base with Mounting Ring
- B Side Entry Tube, Flat Base, no Mounting Ring
- C Back Entry 2mm Spout, Flat Base with Mounting Ring
- D Back Entry 2mm Spout, Flat base, no Mounting Ring
- E Side Entry Tube, Flexible Base (Double Volume)

3. Colour Option



- A Black
- C White
- E Brown
- B Grey
- D Red
- F Green

4. Tube Type


- A Black PVC Tubing with 3mm I/D and 6mm O/D
- B Clear PVC Tubing with 3mm I/D and 6mm O/D
- C Black PU Tube with 1.5mm I/D and 3mm O/D
- D Black PU Curly Coil with 1.5mm I/D and 3mm O/D (please select option 8G below)
- Z No Tubing required

5. Tube Length


- A 1.5 Metres
- C 3 Metres
- E 5 Metres
- G Curly tube
- B 2 Metres
- D 4 Metres
- F 6 Metres
- Z None supplied



6871-0C / AC



6872-00 / 0C / A0 / AC



6872-H0 / HC

Benefits

- ❖ UL approved compact and economical switches
- ❖ Ideal for OEM applications

- ❖ Base or side entry
- ❖ Choice of alternate and momentary actions available

Model No	6871-0C	6871-AC	6872-0C	6872-AC	6872-HC
Switch Details Number of Poles & Action	1 pole C/O momentary	1 pole C/O alternate	2 pole C/O momentary	2 pole C/O alternate	2 pole C/O 1 pole momentary 1 pole alternate
Air Connection	Back entry	Back entry	Back entry	Back entry	Back entry
Air Spout Diameter	4mm	4mm	4mm	4mm	4mm
Connecting Tube Part Number	2311-08	2311-08	2311-08	2311-08	2311-08
Alternative Air Connection Model Number	Back entry 2mm spout 6871-0K side entry 4mm spout 6871-01	Back entry 2mm spout 6871-AK side entry 4mm spout 6871-AO	Back entry 2mm spout 6872-0K side entry 4mm spout 6872-00	Back entry 2mm spout 6872-AK side entry 4mm spout 6872-A0	Back entry 2mm spout 6872-HK side entry 4mm spout 6872-HO
Body Material	Acetal	Acetal	Acetal	Acetal	Acetal
Diaphragm Material	Silicone	Silicone	Silicone	Silicone	Silicone
Electrical rating @ 250V ac	16A Res 4A Ind 1/2 HP	16A Res 4A Ind 1/2 HP	21A (8A) 250V 2HP 250V ac 1HP 125V ac	21A (8A) 250V 2HP 250V ac 1HP 125V ac	21A (8A) 250V 2HP 250V ac 1HP 125V ac
Special Approvals Upon request	UL CSA	UL CSA	UL CSA	UL CSA	UL CSA

All European electrical switch approvals apply.

- ❖ 6872 Variants can be obtained with double diaphragm upon request.