

Industrial Torque Wrenches



The robust construction of this wrench gives accurate results to $\pm 4\%$ even in arduous working conditions. The break action improves accuracy by reducing the possibility of over torquing and gives an unmistakable signal. These wrenches are supplied with a traceable calibration certificate that should satisfy the requirements of BS5750/ISO9000.

493992

Model	Torque Range		Length		Square Drive	Order Code	Price Each
	(Nm)	(lbf.ft)	(mm)	(in)			
3AR	100 - 500	70 - 350	915	36	3/4	137-4366	
3AR/01	100 - 500	70 - 350	1090	43	1	137-5294	
4R	150 - 700	100 - 500	1090	43	3/4	137-5289	
4AR	200 - 800	150 - 600	1140	44.9	3/4	137-5293	
4AR/01	200 - 800	150 - 600	1140	44.9	1	137-5296	
5R	300 - 1000	200 - 750	1470	57.9	3/4	137-5290	
5R/01	300 - 1000	200 - 750	1470	57.9	1	137-5297	
5AR	700 - 1500	500 - 1000	1470	57.9	3/4	137-5291	
5AR/01	700 - 1500	500 - 1000	1470	57.9	1	137-5298	