

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191930120](#)
Status: **Active**
Description: VersaKrimp™ Ring Tongue Terminal for 10-12 AWG Wire

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family Ring and Spade Terminals
Series [19193](#)
Comments Type I Noninsulated; Class 1 and 2
Mil-Spec AS20659-106
Mil-Spec MS20659-106
Product Name VersaKrimp™
Type Ring

Physical
Barrel Type Closed - Brazed
Insulation None
Material - Plating Mating Tin
Packaging Type Bag
Plating min: Mating (µin) 100
Plating min: Mating (µm) 2.5
Plating min: Termination (µin) 100
Plating min: Termination (µm) 2.5
Stud Size 5/16" (M8)
Termination Interface: Style Crimp or Compression
Wire Size AWG 10
Wire Size AWG 12
Wire Size mm² 3.00 - 5.40

Electrical
CSA LR18689
UL E32244

Material Info
Old Part Number C-330-56

Reference - Drawing Numbers
Sales Drawing SD-19193-024



Series image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Halogen-Free
Status
Halogen-Free



Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19193 Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	0640030100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640070100