

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [50-57-9015](#)
Status: **Active**
Overview: [SL™ Modular Connectors](#)
Description: 2.54mm Pitch SL™ Crimp Housing, Single Row, Version A, Non-polarized, 15 Circuits

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-70058 \(PDF\)](#)
[Product Specification PS-70400 \(PDF\)](#)
[Product Specification PS-71851 \(PDF\)](#)
[Test Summary TS-70058-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	LR19980
TUV	R72081037
UL	E29179

General

Product Family	Crimp Housings
Series	70066
Application	Signal, Wire-to-Board
Comments	Version A
Overview	SL™ Modular Connectors
Product Name	SL™
UPC	800753578258

Physical

Circuits (maximum)	15
Color - Resin	Black
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Polyester Alloy
Net Weight	0.107/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	Yes
Temperature Range - Operating	-40°C to +105°C

Material Info

Old Part Number	70066-0014
-----------------	------------

Reference - Drawing Numbers

Product Specification	PS-70058, PS-70400, PS-71851
Sales Drawing	SD-70066-0001-0024
Test Summary	TS-70058-001




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[70066Series](#)

Mates With
[8624](#) , [70203](#) , [70206](#) , [42375](#) , [42377](#)

Use With
SL™ Crimp Terminal [70058](#) , [71851](#)