



GREENLEE®
A Textron Company

MADE FOR THE TRADE!™

WIRE FERL INSUL

Insulated Wire Ferrules



Image
Unavailable

Cat No: 170/WL

UPC No: 783310048473

Description

- Terminate stranded wire into terminal blocks
- Electrolytic copper and tin plating provide maximum conductivity and low contact resistance

Specifications

- Color : White
- Color Code : Old DIN Standard
- Dimension Inches L2 : 0.471 IN (12.000 MM)
- Finish : Tin Plated
- Insulation : Polypropylene Plastic
- Material : Electrolytic Copper
- Recommended Crimping Tools : K1GL, K32GL, K36GL, K30GL, Die 03283
- Size : 0.724 IN (18.400 MM) Overall Length, 0.471 IN (12.000 MM) Sleeve Length
- Standard : CSA, LR 702418, NRTL/C, RoHS
- Type : Insulated
- Wire Size : 18 AWG (0.750 SQ-MM)
- Wire Type : Stranded