

Technical drawing of a label with dimensions and tolerances. The label is rectangular with a white imprint area on the left and a clear area on the right. The drawing includes the following dimensions and tolerances:

- Overall width: $11.0 \pm .062$ [279 ± 1.6]
- Overall height: $8.5 \pm .062$ [216 ± 1.6]
- White imprint area width: $.38 \pm .062$ [9.52 ± 1.6]
- White imprint area height: $1.25 \pm .062$ [31.75 ± 1.6]
- Clear area width: $1.00 \pm .062$ [25.40 ± 1.6]
- Clear area height: $1.00 \pm .062$ [25.40 ± 1.6]
- Printer lead edge feed in the direction: 4
- Laser inkjet labels: S050X125VAJ
- Typical values: TYP. 8 PLCS. (for white imprint area), TYP. 7 PLCS. (for clear area)

PART NUMBER	MATERIAL	MARKER SIZE inches [mm]	LABELS PER SHEET	SHEET QTY.	STANDARD PKG. QTY.
S100X125YAJ	6MY6 CLEAR POLYESTER FILM	1.000 [25.4] X X 0.750 [19.0]	56	45	2500

CAD FILENAME/LAYERS		I00472CD_DC_C I0204/02C	
PANDUIT CORP. TINLEY PARK, ILLINOIS			
CUSTOMER DRAWING OPTIMUMM SELF-LAM. LASER INKJET PRINTABLE LABELS			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .025 (.XX) ± .062 ANGLES ± 		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY RVU		SCALE NTS	
DATE 9/22/04		DRAWING NO. C10204	
CHK'D		DWG A SIZE	
SEE TABLE			