


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [74547-7060](#)
Status: **Active**
Overview: [iPass™ Connector System](#)
Description: External iPass™ Mini Multi-Lane SAS-to-4X LaneLink™ Latching Cable Assembly, 26 Circuits, 28 AWG, 6.0m Length, Key 2, 7



Series

image - Reference only

Documents:
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	74547
Assembly Configuration	Dual Ended Connectors
Comments	CX4 to LaneLink™
Connector to Connector	4X Plug-to-4X Plug
Overview	iPass™ Connector System
Product Name	4X, iPass™, LaneLink™, Mini Multi-Lane, Multi-Lane
UPC	800756718880

Physical

Cable Length	6.0m
Circuits (Loaded)	26
Color - Resin	Black
Gender	Plug
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze, Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic, PVC
Packaging Type	Bag
Pitch - Mating Interface	0.80mm
Plating min - Mating	1.016µm
Plating min - Termination	3.048µm
Single Ended	No
Termination Interface: Style	Surface Mount
Waterproof / Dustproof	Yes
Wire Insulation Diameter	N/A
Wire Size AWG	28
Wire/Cable Type	Parallel Pair

Electrical

Impedance	100#
Shield Type	AL Foil
Shielded	Yes
Voltage - Maximum	30V

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-74547-700
---------------	--------------

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[74547Series](#)

Mates With

[75586](#) iPass™ Surface Mount Receptacle.
[74548](#) EMI Housing Assembly

Use With

[74735](#) X2 Transceiver. [74739](#) XPAK
Transceiver. [74548](#) Guide Rail