

Straight Blade Devices

Miscellaneous and Combination Receptacles

2 Pole, 3 Wire Grounding

15 and 20 Ampere



15A 125V
NEMA 5-15R
UL CSA

Miscellaneous Receptacles

Description	Catalog Numbers
Receptacle, display type, brown phenolic, with .060 in. brass plate and blank flush plug.	HBL5236
Replacement receptacle for HBL5236.	HBL5236M2
Replacement threaded plug for HBL5236.	D5590401*
Receptacle, wooden floors, brown phenolic with .060 in. brass plate, blank flush plug and box.	HBL6236
Receptacle, clock hanger, brown with stainless steel plate.	HBL5235
Four outlet cluster, brown phenolic, steel cover, swivel hook. Cord grip range .296-.562 in. (7.5-14.3) cord not supplied.	HBL9259*

Note: *Not UL Listed or CSA certified.





HBL5236




HBL5235


Special Combination Duplex Receptacles

Description	Catalog Numbers
15A, 125V  Brown RTP, 1 feed, 1 return, back/side wired	HBL4792
15A, 125V  Brown RTP, 2 feeds, 1 return, side wired	HBL4794
15A, 125V  Brown RTP, 2 feeds, 2 returns, side wired	HBL4795
15A, 250V  Brown nylon face, 2 circuit, back and side wired	HBL5292
15A, 250V  Ivory nylon face, 2 circuit, back and side wired	HBL5292I
15A, 125V  Brown nylon face, 2 circuit, back and side wired	HBL5492
20A, 250V  Ivory nylon face, 2 circuit, back and side wired	HBL5492I
20A, 125V  Brown RTP, 2 feeds, 1 return, common ground	HBL7371
10A, 250V  15A, 125V  Note: This device is not listed by Underwriters Laboratories Inc. nor CSA certified.	
20A, 125V Brown nylon, side and back wired	HBL5392
20A, 125V Note: This device will only accept 20A grounding plugs.	

Note: RTP is an abbreviation for reinforced thermoplastic polyester.
See page A-44 for accessories.



HBL9259



HBL5292