


ED2205/X



1-n poles, Spacing 5.0 mm

insert required no. of poles **x**

How to order see page 5



Ratings:

Rated Voltage

300V

250 V

Rated Current

20 A

24 A (T60)

Wire Size

AWG 30-12

2.5 mm²

Test Voltage

2.0 kV

Rated Torque/ScrewSize

0.5 Nm/M2.5

Max. Rated Cross Section

Single Wire (solid)

2.5 mm²

Stranded Wire (flexible)

2.5 mm²

Stranded wire with Ferrules

2.5 mm²

Dimensions

Spacing

5.0 mm

PCB Hole Diameter

1.3 mm

Stripped Length

9.0 mm

Materials

Insulating Material

PA

Flammability Class

UL94 V-0

Temperature Range

-30°C/+105°C

Clamp Cage


Fe/Fe

Wire Guard

Cu

Color

Green



P = No. of poles