

Customer Information Sheet

DRAWING No.: D830XXC-46

SHEET 2 OF 2




IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



ORDER CODE:

D830XXC-46

NUMBER OF CONTACTS

(SEE TABLE)

FINISH

46 = 100% TIN

SPECIFICATION:

MATERIAL:

MOULDING - PPS (BROWN) UL94V-0

CONTACTS - PHOSPHOR BRONZE

FINISH:

46 = 100% TIN OVER NICKEL

ELECTRICAL:

CURRENT RATING - 1A

CONTACT RESISTANCE = 30 MILLIOHMS MAX

INSULATION RESISTANCE = 1000 MEGOHMS MIN

DIELECTRIC STRENGTH = 600V AC (1 MINUTE)

ENVIRONMENTAL:

OPERATING TEMPERATURE = -50°C TO +105°C

SOLDERING TEMPERATURE = 260°C FOR 5 SECONDS

PACKING: TUBE

NOTES:

1. FOR ELECTRICAL AND MECHANICAL SPECIFICATION

SEE COMPONENT SPECIFICATION C020XX (LATEST ISSUE).

2. ALL TOLERANCES ARE ±0.25 UNLESS OTHERWISE STATED.

No. OF CONTACTS	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'
20	15.50	15.50	5.08	5.08
28	18.04	18.04	7.62	7.62
32	18.04	20.60	7.62	10.16
44	23.48	23.48	12.70	12.70
52	25.88	25.88	15.24	15.24
68	31.04	31.04	20.32	20.32
84	36.04	36.04	25.40	25.40

JMB	10	19.10.06	9530
NAME	ISS.	DATE	C/NOTE
APPROVED:	JMB		
CHECKED:	NBC		
DRAWN:	W J. BOURNE		
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA:

mm²

TITLE:

LOW PROFILE PC TAIL
PLCC SOCKET

DRAWING NUMBER:

D830XXC-46

SHT
2
OF
2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

[D83020C-46](#) [D83028C-46](#) [D83032C-46](#) [D83044C-46](#) [D83052C-46](#) [D83068C-46](#) [D83084C-46](#)