

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202310117](#)
Status: **Active**
Overview: [Brad M23 Signal and Power Connectors](#)
Description: Brad M23 Signal Connector, Back Panel-Mount Receptacle, Straight Male Single Hole Mount M25x1.5, PCB Contacts, 19 (16+3) Poles

Documents:
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Field Attachable / Accessories
Series	120231
Application	Signal
Comments	PCB Contacts 0.14-1.00mm² / 0.56-1.50mm², PCB Contacts 0.14-1.00mm² / 0.56-1.50mm²
IP Rating	IP67
Material - Contact	Brass
Overview	Brad M23 Signal and Power Connectors
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906301125
Physical	
Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	Nylon
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Orientation	Straight
Poles	19 (16+3)
Temperature Range - Operating	-40°C to +125°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	10.0A, 8.0A
Voltage - Maximum	150V
Material Info	
Engineering Number	KRSLP46-770
Reference - Drawing Numbers	
Sales Drawing	SD-120231-005



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[120231](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION